





ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33341417	01	CODE A	ALL PARTS VO / 20,5
33341418	01	CODE B	
33341419	01	CODE C	
33341420	01	CODE D	
33346281	01	CODE A	ALL PARTS NVO / 19,9
33347538	01	CODE B	
33347539	01	CODE C	
33347541	01	CODE D	


POSITION	1		2								3	4		5	
NAME	HOUSING		INSERT								HOUSING SEAL	SECONDARY LOCK		SLIDER	
MATERIAL	PBT GF30 FR17	PBT GF30	PBT GF30 FR17				PBT GF30				LSR 50 SHORE	PBT GF30 FR17	PBT GF30	PBT GF30 FR17	PBT GF30
COLOR:	BLACK	BLACK	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	REDDISH-BROWN	ORANGE	YELLOW	ORANGE	YELLOW
PART-NO.:	33282971	33344858	33338840	33338841	33338894	33338895	33346021	33347341	33347342	33347343	33283921	33338896	33344872	33282491	33344853
-	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---
-	1	---	1	---	---	---	---	---	---	---	1	1	---	1	---
-	1	---	---	1	---	---	---	---	---	---	1	1	---	1	---
-	1	---	---	---	1	---	---	---	---	---	1	1	---	1	---
-	1	---	---	---	---	1	---	---	---	---	1	1	---	1	---
-	---	1	---	---	---	---	1	---	---	---	1	---	1	---	1
-	---	1	---	---	---	---	---	1	---	---	1	---	1	---	1
-	---	1	---	---	---	---	---	---	1	---	1	---	1	---	1
-	---	1	---	---	---	---	---	---	---	1	1	---	1	---	1

DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P/CHG						
19NO18	R	01			INITIAL RELEASE		P.BAL	P.NAJ	M.GRU
14MR19	R	01	AA	B6	REFERENCE HELLERMANN TYTON DWG-NO. ADDED		K.FAR	M.GRU	K.PIT
27OC20	R	01	AB	G11 B6	PART AVAILABILITY FOR PART NUMBERS 33346281, 33347538, 33347539, 33347541 UPDATED NOTES UPDATED		P.NAJ	M.GRU	


CLOSED POSITION




SCALE
1:1




CODE A




CODE C



CODE B



CODE D



NOTES

- ON MAIN VIEW ASSEMBLY 33341417 SHOWN (CODE A)
- DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK AND SLIDER IN OPEN POSITION
- ASSEMBLY INSTRUCTION NO.:
 - 35269106-CUS71 - PRELIMINARY ASSEMBLY
 - 35269106-CUS72 - HARNESS ASSEMBLY
 - 35269103-CUS73 - CAR ASSEMBLY
 - 35269102-CUS73 - CAR ASSEMBLY
- MATING PARTS:
 - 8 WAY 1.5 MALE PANEL MOUNT ASM DWG-NO.: 35153950
 - 8 WAY 1.5 MALE STRAP MOUNT ASM DWG-NO.: 35153957
 - BACKSHELL 90 DEG APTIV DWG-NO.: 35024554 (HT DWG-NO.: 17-2275-001-CSG)
 - BACKSHELL 180 DEG APTIV DWG-NO.: 35024538 (HT DWG-NO.: 17-1461-001-CSG)
 - PROTECTION CAP APTIV DWG-NO.: 35149886 (HT DWG-NO.: 17-2266-001-CSG)
- MATING TERMINAL SYSTEM:
 - 1.5 TERMINAL DWG-NO.: 15432214
 - MAX WIRE CROSS SECTION: 1.0MM²
 - RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1.5MM² - USE COMBINATION: TE TERMINAL: MCP 1.5, DWG NO.: 1418884-3
 - SEAL: 964972-1
 - MAX INSULATION CRIMP DIMENSIONS: HEIGHT: 3.40; WIDTH: 3.30
- 1 APTIV LOGO
- 2 MATERIAL NAME ACCORDING TO VDA 260
- 3 TOOL CAVITY NUMBER
- 4 PART CAVITY NUMBER
- 5 MOVING DISTANCE OF SECONDARY LOCK
- 6 MOVING DISTANCE OF SLIDER

DIM TO CHECK	DIMENSIONAL RANGE (MM)										CHART	TOLERANCE UNLESS OTHERWISE SPECIFIED
	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300		
1) DIM FOR HELP	TO	30	70	100	150	200	250	300	400			
TOLERANCE UNLESS OTHERWISE SPECIFIED												
ANGULAR TOLERANCE ±2°												

DWG TYP		DISTR CODE
PART DRAWING		
WEIGHT (GR)	SEE CHART	
VOLUME (CM ³)	---	
ROUTING		D
UNLESS OTHERWISE SPECIFIED		
GENERAL TOLERANCES ACCORDING TO:		
SEE CHART		
GD&T ACCORDING TO:		ISO 1101
FIRST ANGLE PROJECTION		
DO NOT SCALE		
USE MATH DATA		

• APTIV •

CONNECTION SYSTEMS
KRAKOW, POLAND
COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WLASNOSCIA APTIV I ZAWIERA POUFNE INFORMACJE. POWIELANIE, ROZPOWIECZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEKOLWIEK ICH ZAWARTOSCÍ BEZ NADANIA WYRAŻNYCH UPRAWNIENÍ, JEST ZABRONIONE.

DR	DATE
P.BALAJI	18NO18
P.NAJDUCH	19NO18
M.GRUDZEWSKI	20NO18
APVD3	
APVD4	
APVD5	

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIIE PRZETWORZONE OKRESLA APTIV 10949001

SEE CHART

DRAWING NAME

8 WAY 1.5
CTCS FEMALE ASSEMBLY

DRAWING NUMBER

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	2:1	1 OF 1	1 OF 1	R	01	AB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33341420](#)