





3 ±0.1
2 ±0.1

VAR	COD	PART-NO.:
0	C	15509588
1	C	15509590
2	C	15509611
3	C	15509598
4	C	33139159
5	C	33139155
6	C	33231216

SCALE:
1 : 1



3 ±0.1
4.7 ±0.1

0	C	FEMALE HOUSING 48 WAY ASM	15509588	03	15MR13	---	---	---	---	CONDITION OF DELIVERY, POS. 3,4,5 ASSEMBLED
-	3	FEMALE HOUSING 48 WAY	15509575	---	---	1	PBT GF20 YEL	1021	---	ONLY ASSEMBLED PARTS AVAILABLE
-	4	SECONDARY LOCK	15509562	---	---	1	PBT GF20 GRN	6001	---	ONLY ASSEMBLED PARTS AVAILABLE
-	5	HOUSING SEAL	13883892	---	---	1	SILICON RED BRN	3011	---	ONLY ASSEMBLED PARTS AVAILABLE
1	C	FEMALE HOUSING 48 WAY ASM	15509590	03	15MR13	---	---	---	---	CONDITION OF DELIVERY, POS. 4,5,6 ASSEMBLED
-	6	FEMALE HOUSING 48 WAY	15509576	---	---	1	PBT GF20 YEL	1021	---	ONLY ASSEMBLED PARTS AVAILABLE
-	4	SECONDARY LOCK	15509562	---	---	1	PBT GF20 GRN	6001	---	ONLY ASSEMBLED PARTS AVAILABLE
-	5	HOUSING SEAL	13883892	---	---	1	SILICON RED BRN	3011	---	ONLY ASSEMBLED PARTS AVAILABLE
2	C	FEMALE HOUSING 48 WAY ASM	15509611	03	15MR13	---	---	---	---	CONDITION OF DELIVERY, POS. 4,5,7 ASSEMBLED
-	7	FEMALE HOUSING 48 WAY	15509583	---	---	1	PBT GF20 YEL	1021	---	ONLY ASSEMBLED PARTS AVAILABLE
-	4	SECONDARY LOCK	15509562	---	---	1	PBT GF20 GRN	6001	---	ONLY ASSEMBLED PARTS AVAILABLE
-	5	HOUSING SEAL	13883892	---	---	1	SILICON RED BRN	3011	---	ONLY ASSEMBLED PARTS AVAILABLE
3	C	FEMALE HOUSING 48 WAY ASM	15509598	03	15MR13	---	---	---	---	CONDITION OF DELIVERY, POS. 4,5,8 ASSEMBLED
-	8	FEMALE HOUSING 48 WAY	15509582	---	---	1	PBT GF20 YEL	1021	---	ONLY ASSEMBLED PARTS AVAILABLE

D
C
B
A

TITLE	PART-NO.	CABLE CROSS SECTION (MM ²)	MATERIAL	NOTES
FEMALE TERMINAL MCP 6.3	I24I412-I	0.5 - 1.0	Cu Ni Si	OR SIMILAR
	I24I414-I	>1.0 - 2.5	Cu Ni Si	OR SIMILAR
	I24I416-I	>2.5 - 4.0	Cu Ni Si	OR SIMILAR
FEMALE TERMINAL ATS 2.8	I5344659	0.35 - 0.5	Cu Ni Si	OR SIMILAR
	I5344661	0.75 - 1.0	Cu Ni Si	OR SIMILAR
	I5344660	1.5 - 2.5	Cu Ni Si	OR SIMILAR
FEMALE TERMINAL JPT 2.8	964282-I	0.35-0.5	Cu Fe 2	OR SIMILAR
	964286-I	0.5 - 1.0	Cu Fe 2	OR SIMILAR
	964273-I	1.5 - 2.5	Cu Fe 2	OR SIMILAR
FEMALE TERMINAL CTS 1.5	I5432208	0.35	Cu Fe 2	OR SIMILAR
	I5432210	0.5 - 1.0	Cu Fe 2	OR SIMILAR
	I5432212	1.0 - 1.5	Cu Fe 2	OR SIMILAR
FEMALE TERMINAL MCP 1.5	I564324-I	0.35	Cu Ni Si	OR SIMILAR
	I214380-I	0.5 - 1.0	Cu Ni Si	OR SIMILAR
	I418884-I	1.5	Cu Ni Si	OR SIMILAR

TITLE	PART-NO.	CABLE DIAMETER	MATERIAL
CABLE SEAL MCP 6.3	I5363779	1.2 - 2.0	SILICONE YEL
	I5363604	2.0 - 2.7	SILICONE WHT
	I5327864	2.8 - 3.8	SILICONE RED BRN
CAVITY PLUG	35232480	---	SILICONE GRA
CABLE SEAL JPT 2.8 / ATS 2.8	I5327860	1.2 - 2.0	SILICONE BLU
	I5327863	2.0 - 2.7	SILICONE RED BRN
	I5327859	2.7 - 2.9	SILICONE YEL
CAVITY PLUG	I5337197	---	SILICONE WHT
	I0730124	---	SILICONE GRN
CABLE SEAL MCP 1.5 / CTS 1.5	I5327913	1.2 - 1.6	SILICONE RED
	I5327918	1.4 - 2.0	SILICONE GRA
	I5339412	1.9 - 2.1	SILICONE YEL
CAVITY PLUG	964972-I	1.9 - 2.4	SILICONE YEL
	I2198198	---	SILICONE WHT

(13A)

TITLE	PART-NO.:	CABLE DIAMETER	MATERIAL
CABLE SEAL MCP 6.3	15363779	1.2 - 2.0	SILICONE YEL
	15363604	2.0 - 2.7	SILICONE WHI
	15327864	2.8 - 3.8	SILICONE RED BRN
CAVITY PLUG	35232480	---	SILICONE GRA
CABLE SEAL JPT 2.8 / ATS 2.8	15327860	1.2 - 2.0	SILICONE BLU
	15327863	2.0 - 2.7	SILICONE RED BRN
	15327859	2.7 - 2.9	SILICONE YEL
CAVITY PLUG	15337197	---	SILICONE WHI
	10730124	---	SILICONE GRN
CABLE SEAL MCP 1.5 / CTS 1.5	15327913	1.2 - 1.6	SILICONE RED
	15327918	1.4 - 2.0	SILICONE GRA
	15339412	1.9 - 2.1	SILICONE YEL
	964972-1	1.9 - 2.4	SILICONE YEL
CAVITY PLUG	12198198	---	SILICONE WHI

	7	6	5	4	3	2	1	0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15509585](#)