



SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL □ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF INSPECTIONS REQUIRED	17
	LAST NO. USED	17

MISSING SYMBOLS		
		NO MISSING SYMBOL NUMBER

DWG STATUS		ZONE		REVISION HISTORY		AUTH		DR APPROV	
15DE15	R 01	-	-	ALL PARTS - RELEASED PART DRAWING		431562	NRW	MAX	MAX
05AP16	R 02	-	-	ALL PARTS - ADDED NOTES #4-6		432660	CGD	CSO	WAL
21JA16	R 03	-	-	ALL PARTS - UPDATED CONN TO LATEST REV		433416	ABH	WAL	WAL
100C16	R 04	-	-	33299856, 33299858-59 - UPDATED PDM ATTRIBUTES		434483	APB	APB	WAL
20JA17	R 05	-	-	ALL PARTS - DRAWING NAME WAS TAXI ASM CONN B F OCS 1.2 MODULAR		436949	GLB	GLB	WAL
01SE17	R 06	-	-	ALL PARTS - ADDED CUSTOMER DRAWING REFERENCE NOTE		437625	AHY	AHY	WAL
30JA18	R 07	-	-	ALL PARTS REVISED TOL ON DIM 16; NO REV UPDATE REQ'D		438894	CM	CM	WAL
25JA18	R 08	-	-	ADDED "SHT 1 OF 2"		441973	AGC	AGC	WAL

- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-CS-01.
 - THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-CS-01.
 - FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
 - INDEPENDENT SECONDARY LOCK RETENTION FORCE OF SEATED ISL 55N MAXIMUM.
 - TERMINAL INSERTION FORCE INTO CONNECTOR WITH SECONDARY LOCK SEATED FOR CABLE >1.0 MM; TERMINAL WILL NOT FULLY SEAT AND LOCK AT MINIMUM FORCE OF 32N.
 - SECONDARY LOCK PRE-STAGE INSERTION 65N MAXIMUM.
 - FOR FCA CUSTOMER DRAWING REFER TO 33255742-CU502-501.

33299859	02	AC	106	33255756	33255757
33299858	02	AC	105	33255755	33255757
33299856	02	AC	104	33255754	33255757
33299855	02	AB	103	33255753	33255757
33299854	02	AB	102	33255752	33255757
33299853	02	AB	101	33255751	33255757

DIMENSIONAL RANGE (MM)												CHART E	
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 300	> 400		
TO	20	30	70	100	150	200	250	300	400				
TOLERANCE UNLESS OTHERWISE SPECIFIED													
	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33299853](#)