






TABLEAU DES CODEURS - CODING TABLE



CODEUR CODING	COULEUR COLOUR	REFERENCE F.C.C. F.C.C. PART NUMBER	REFERENCE VOLVO VOLVO PART NUMBER
1	BLANC - WHITE	211 PL 12 3 S 9 004	9148277
2	ROUGE - RED	211 PL 12 3 S 2 004	9148278
3	JAUNE - YELLOW	211 PL 12 3 S 4 004	9148279
4	BLEU CIEL - LIGHT BLUE	211 PL 12 3 S 6 004	9148280
5	VERT CLAIR - LIGHT GREEN	211 PL 12 3 S 5 004	9148281
SANS - WITHOUT	BEIGE - BEIGE	211 PL 12 3 S 1 004	9162001



- NOTE
- 1 GENERAL RADIUS R=0.50
RAYONS NON COTES R=0.50
 - 2 MARKING RAW MATERIAL
IDENTIFICATION MATIERE VOLVO STD 5052,41
 - 3 CAVITY NUMBER
N°D'EMPREINTE VOLVO STD 5051,15
 - 4 VOLVO IDENTIFICATION AND PART NUMBER
IDENTIFICATION ET REFERENCE VOLVO VOLVO STD 5051,15
 - 5 SPC DIMENSION
COTE MSP

CONNECTIQUE SICMA 2

ARCHIVE LE 21/11/00

IND.	MODIFIE COTE MSP	GERARD MILLOT	23/07/1993	A 96 072
DESIGNE LE: 21/03/1994	VERIFIE LE: 03/09/94	NOM	DATE	N° Bordereau
PAR: F. FAURIE	PAR: F. FAURIE	MATIERE: PBT	TOLERANCE GENERALE	ECHELLE: 2 / 1
TRAITEMENT:	POIDS:	ETAT: -	± 0.10 ± -	
		SURFACE:	RUGOSITE:	

Ce document est la propriété de FRAMATOME CONNECTORS CONNECTRAL. Il ne peut être reproduit ou communiqué sans son autorisation.

MODULE LANGUETTES 12 VOIES
12 WAY MALE MODULE
2.8 X 0.8

FRAMATOME CONNECTORS
CONNECTRAL
Rue des Quatre Filles - BP 25
28231 EPERNON cedex FRANCE

A2 211FT0062

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[211PL123S9004](#) [211PL123S9004-B](#) [211PL123S1004](#) [211PL123S5004-B](#) [211PL123S5004](#) [211PL123S4004](#)
[211PL123S6004](#) [211PL123S2004](#)