SYMBOL DEFINITION		MISSING SYMBOLS
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ( ) DOES NOT REQUIRE INSPECTION., IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED: 114	NO MISSING SYMBOL NUMBER
	LAST NO. USED: 40	

DWG STATUS DATE	SIZE	REV	N/P	CHG	ZONE	REVISION HISTORY	AUTH	DR	APVD
27AP15	R	01	-	-	-	ALL PARTS - CREATED PART DRAWING	427871	KV	KV TKS
25SE15	R	02	-	-	-	3321399-02- PSD WAS-DIM #23 3276719-22- RELEASED PART DRAWING	430423	KV	KV TKS
20JL16	R	03	-	-	-	REVISED GRAPHICS	433565	SM	SM TKS
06SE17	R	04	-	-	-	ALL PARTS - ADDED CORRUGATED TUBE & *CABLE TIE WIDTH* NOTES., CONN BODY COLOR COLUMN AND RENUMBED UL94 FLAMMABILITY COLUMN	437278	JVM	JVM TKS
16NO18	R	05	-	-	-	ALL PART - REVISED DIM #36 3321399 - UPDATED PART AVAILABILITY	441624	KRK	KRK KST
24JN19	R	06	-	-	-	3321201 - UPDATED PART AVAILABILITY	443727	DL	SNS KST
02OC19	R	07	-	-	-	3321200 - UPDATED PART AVAILABILITY	550166	JAA	JAA KST
30JA20	R	08	-	-	-	3276719 - UPDATED PART AVAILABILITY	550918	LGD	JAA KST



TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 103
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 104
SAME AS TYPE 101
EXCEPT AS SHOWN



SECTION A-A





SECTION B-B



TYPE 101







NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

   DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM. MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER EANP.4-3.CS.01.EN.

3. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.

4. DESIGNED FOR CORRUGATED TUBE NW26

5. MAXIMUM CABLE TIE WIDTH 5 MM

3327672 2	02	AB	104	3327671 8	GREEN	3327672 3	3327377 4	3319886 9	V-0
3327672 1	02	AB	103	3327671 7	BLUE	3327672 3	3327377 4	3319886 9	V-0
3327672 0	02	AB	102	3327671 6	GRAY	3327672 3	3327377 4	3319886 9	V-0
3327671 9	02	AC	101	3327671 5	BLACK	3327672 3	3327377 4	3319886 9	V-0
3321320 2	02	AB	104	3321319 7	GREEN	3321319 2	3321319 3	3319886 9	-
3321320 1	02	AC	101	3321319 6	BLUE	3321319 2	3321319 3	3319886 9	-
3321320 0	02	AC	102	3321319 5	GRAY	3321319 2	3321319 3	3319886 9	-
3321319 9	02	AB	101	3321319 4	BLACK	3321319 2	3321319 3	3319886 9	-
PART NO	REV	N/P	TYPE	CONN	CONN BODY COLOR	INNER CONN	LOCK SLC	SEAL CONN	UL94 FLAMMABILITY STD

DRAWING NUMBER: 3321 3203							
SIZE	SCALE	FRAME NO	SHEET NO	TOTS	REV	N/P
A1x3	2:1	2 OF 2	1 OF 1	R	08	-

(16) PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN ( ) INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE SHALL BE ESTABLISHED

DIMENSIONAL RANGE (MM)								
FROM	0.5	3.01	6.01	30.01	120.01	400.01	1000.01	2000.01
TO	3	6	30	120	400	1000	2000	3000
TOLERANCE UNLESS OTHERWISE SPECIFIED	±0.05	±0.1	±0.2	±0.3	±0.5	±1	±2	±3

THIRD ANGLE PROJECTION	DO NOT SCALE	USE MATH DATA	NX

APVD:	V.KANDASAMY	24AP15	B
APVD:	V.KANDASAMY	24AP15	
APVD:	TURNER KEVIN S	27AP15	
APVD:			
APVD:			

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV STANDARDS

SIZE: SEE CHART

DRAWING NAME: TAX1 ASM CONN 62 M CTS SLD

DRAWING NUMBER: 3321 3203

SIZE	SCALE	FRAME NO	SHEET NO	TOTS	REV	N/P
A1x3	2:1	1 OF 2	1 OF 1	R	08	-

A ( ) LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.

PART NUMBERS THAT DO NOT HAVE A ( ) LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.

CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.

DWG TYPE: PART DRAWING

STYLE:

VOLUME (CM³):

SYSTEM SIZE: D

UNLESS OTHERWISE SPECIFIED

THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED. GENERAL TOLERANCING ASSEMBLY RULES: SEPARATE PATTERNS OF FEATURES MAY BE SHOWN SEPARATELY REGARDLESS OF DATUM REFERENCES.

ALL DIMENSIONS ARE IN MILLIMETERS

REFERENCE:

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL AND PROPRIETARY INFORMATION. ANY REPRODUCTION OR UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD WITH DATA, AS WELL AS COMMUNICATION OF ANY CONTENTS TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

COPYRIGHT 2015 APTIV, ALL RIGHTS RESERVED.

•APTIV•
CONNECTION SYSTEMS
Chennai, India

3321 3203

Plotted: 09-MAR-20 11:44:49 AM
Saved: 09-MAR-20 11:44:49 AM
By: SNS
File: C:\Users\SNS\Desktop\3321 3203 08.dwg

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Aptiv:
33276719