


I	COVER 21 WAY	15396771	PBT 6F10	BLACK
POS.	DESCRIPTION	APTIV PART NUMBER	MATERIAL	COLOR

ASSOCIATED PARTS (FOR INFORMATION)			
DESCRIPTION	APTIV P/N	WIRE SECTION	DIAMETER OF WIRE SIZE
MATING PART	15396772, 15396773	-	-
MQS 0.64 FEMALE SEALED TERMINAL	15341540	-	-

☐ DIM TO CHECK	DIMENSIONAL RANGE (MM)	CHART
FROM TO	> 0 > 20 > 30 > 70 > 100 > 150 > 200 > 250 > 300 > 400	1 2 3 4 5 6 7 8 9 10 11 12
☐ THEORETIC DIM	±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2	1 2 3 4 5 6 7 8 9 10 11 12
	ANGULAR TOLERANCE ±2°	



NOTE	SPECIFICATIONS
1	MALE CONNECTOR ACCORDING TO APTIV SPECIFICATION: CAQE TBD
2	MALE CONNECTOR ACCORDING TO: -TEMPERATURE CLASS TX -ENGINE VIBRATOR CLASS VX -SEALING CLASS EX
3	USER'S MANUAL: TBD
4	DELIVERY CONNECTOR WEIGHT : 7.1g
5	NO WAFER HINGE OR WAFER HINGE BROKEN ALLOWED
6	VISUAL DEFECTS ON NO FUNCTIONNAL AREAS ALLOWED
7	MATERIAL CODE
8	TOOL CAVITY NUMBER
9	PART REVISION NUMBER
10	SUPPLIER LOGO
11	PART NUMBER
12	DATE CLOCK


DWS TYP CUSTOMER PART DRAWING	
WEIGHT (GR)	DISTR CODE
SEE NOTE	D
VOLUME (CM³)	
ROUTING	

UNLESS OTHERWISE SPECIFIED
GENERAL TOLERANCES ACCORDING TO: SEE CHART
GD&T ACCORDING TO: ISO 1101





REFERENCE
FIRST ANGLE PROJECTION
DO NOT SCALE USE MATH DATA

• APTIV •	
CONNECTION SYSTEMS Chennai, India COPYRIGHT 2021 APTIV. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DR	P.BALAJI
APVD1	LAGUETTE MAURICE
APVD2	LAGUETTE MAURICE
APVD3	
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001	
MATERIAL	
SEE TABLE	
DRAWING NAME	
COVER 21 WAY FOR MQS/MTS 0.64 TERMINAL	
DRAWING NUMBER	
15396771	
SIZE	A1
SCALE	5:1
FRAME NO	1 OF 1
SHEET NO	1 OF 1
STG	R 01
REV	
N/P	

3D VIEW



SCALE 1:1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[15396771](#)