



1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF GUT FLANGE AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS, SHOW BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
3. MATING COMPONENTS OR EQUIVALENT:
CONNECTOR 12034482
4. THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
ALL CAVITIES TO ACCEPT 12034047 TERMINAL
CHARACTERS C & D AND 12034048 TERMINAL
5. MATERIAL RECYCLING CODE >PA66/ PER SAE J1344 (2.3X10.1) RAISED
CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE,
OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
6. (2.3X10.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY
EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.

A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.

18AP02	R	02	-	-	ALL PARTS - REVISED CAVITIES GRAPHICS	223874	EOV	EOV	1
30AU02	R	03	-	-	ALL PARTS - REVISED GRAPHICS	229482	EOV	EOV	1
26SE02	R	04	-	-	ALL PARTS - REVISED OPT CONSTRUCTION GRAPHICS	231301	EOV	EOV	1
13DE02	R	05	-	-	ALL PARTS - UPDATED PDM ATTRIBUTES	234643	HH	EOV	1

[illegible]

12034481	011	AD		M320212 P66 1H HS GRA LT	6.220	
12015345	011	AD		M3592001 P66 1H HS BKL	6.220	
PART NO	REV	N/P	STATUS	MATERIAL SPEC & COLOR	VOLUME CM ³	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12015345](#) [12015345-B](#)