






Front view of the generator showing the nameplate and terminal box. The nameplate includes the model number ZFW13-3, the manufacturer PGT-ASA-GFIS, and the GM logo. The terminal box is on the right side.

VIEW SHOWN WITH MOUNTED SPOUT (ON HARNESS-SIDE)
AND GUIDE-RING (OPEL-PART-Nr. ZUH-199, FCI-Nr. 3 099 04 01)
Ansicht dargestellt mit montierter Tülle (Kabelbaumsseite)
und Sicherungsring (OPEL-Teil-Nr. ZUH-199, FCI-Nr. 3 099 04 01)



VIEW SHOWN WITH MOUNTED SPOUT (ON HARNESS-SIDE)
AND GUIDE-RING (OPEL-PART-NO. ZUH-199, FCI-NO. 3 099 04 01)
Ansicht dargestellt mit montierter Tülle (Kabelbauseitig) F
und Sicherungsteil (OPEL-Teile-Nr. ZUH-199, FCI-Nr. 3 099 04 01)



GUIDE-RING
IF.C. D-R-NO.3 099 04 011
Sicherungsring
IF.C. D-R-Nr.3 099 04 011

		(27.5)	(2
		HOUSING "SHROUD"	
		Gehäuse "Steck-Körper"	
			2 - I - - I - - I - -
24 414 857	ZFW13-3	3 043 03 11 D	
24 414 842	ZFW22-1	3 043 03 01 D	
OPEL-DRAWING-NO. OPEL-Zeichnungs-Nr.	OPEL-PART-NO. OPEL-Teile-Nr.	FCI-PART-NO. & REV. FCI-Teile-Nr. & Index	NO. C. An

2	2	5	BUFFER Gummipuffer	TPV 169;51* Shore A	GM OK003521	NATURE	22-WAY MAL HOUSING FCI-NO. 3 053 02 13-WAY MAL HOUSING FCI-NO. 3 053 02 GUIDE-RING FOR SPOUT FCI-NO. 3 053 02
1	1	4	SLIDER Schieber	PBT-GF30	GM OK006615	BLACK schwarz	
1	1	3	SEAL Dichtung	SILICON		RED rot	
1	1	2	TPA Sek.verriegelung	PBT-GF10	GM OK006612	VIOLET Violett	
1	1	1b	13-WAY FEMALE HOUS. 13-pol. Buchsengeh.	PBT+ASA-GF15	GM OK006612	BLACK schwarz	
1	1	1a	22-WAY FEMALE HOUS. 22-pol. Buchsengeh.	PBT+ASA-GF15	GM OK006612	BLACK Schwarz	

		-	-								9 077 01 0
24 414 857	ZFW13-3	3 043 03 11 D									
24 414 842	ZFW22-1	3 043 03 01 D									
OPEL-DRAWING-NR. OPEL-Zeichnungs-Nr.	OPEL-PART-NR. OPEL-Teile-Nr.	FCI- PART-NR. & REV. FCI- Teile-Nr. & Index	NO. OF ITEMS Anzahl	ITEM POSITION	NAME Benennung	MATERIAL Material	CUSTOMER MATERIAL SPEC. Kunden Werkstoff Spez.	COLOUR Farbe	COMPONENT FRM Gegenstück		

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[30430311](#)