


8200 Series Dissipative Vinyl Three-Layer Mats and Rolls are soft table mats with a three-layer construction that meet ANSI/ESD S20.20 tested per worksurface standard ANSI/ESD STM4.1-2017. The top color layer is durable static dissipative vinyl, which has sufficiently low resistance to discharge static-laden conductors, yet will help prevent the shorting of pins on the backs of printed circuit boards laid on the mat. The middle layer is a highly-conductive scrim that provides the main discharge path to ground, and the bottom layer is static-dissipative foam, providing a durable nonskid cushion. Compatible with Constant Monitors.



Properties	Typical Value
Material	Top Layer - Static Dissipative Vinyl Middle Layer - Highly Conductive Scrim Bottom Layer - Static Dissipative Foam
Color*	Blue, Brown, Gray, Dark Blue
Thickness	0.140" (3.5 mm)
Hardness (top)	78 Shore A
Resistance	
Surface to Ground (Rtg)	$1 \times 10^6$ to $< 1 \times 10^9$ ohms
Surface to Surface (Rtt)	$1 \times 10^6$ to $< 1 \times 10^9$ ohms
Tolerance	Width +/- 0.250" Length +/- 0.250"

\*Color and texture may vary between lots and mills

#### RoHS, REACH and Conflict Minerals, Statement

See the Desco Industries RoHS, REACH, and Conflict Minerals Statement:  
[DescoIndustries.com/RoHS3.aspx](https://www.DescoIndustries.com/RoHS3.aspx)

#### See the SCS Limited Warranty

[StaticControl.Descoindustries.com/Limited-Warranty.aspx](https://www.StaticControl.Descoindustries.com/Limited-Warranty.aspx)

Specifications and procedures subject to change without notice.

# SCS



Made in the  
United States of America

#### Table Mat Kit Item Numbers

Size	Blue	Brown	Gray	Dark Blue
24" x 48" (0.6 m x 1.2 m)	<a href="#">8214</a>	<a href="#">8211</a>	<a href="#">8213</a>	<a href="#">8215</a>
30" x 60" (0.8 m x 1.5 m)				<a href="#">8216</a>

#### Table Mat Kit Includes:

- 1 Table Mat, size as specified
- 1 [3048](#) Wrist Strap Grounding System
- 2 [3050](#) Single Snap Fastener (Snaps installed on long side of mat)

#### Floor Mat Kit Item Numbers

Size	Blue	Gray
48" x 72" (1.2 m x 1.8 m)	<a href="#">8204</a>	<a href="#">8203</a>

#### Floor Mat Kit Includes:

- 1 Floor Mat, size as specified
- 1 [3040](#) 15' (4.6 m) Ground Cord
- 2 [3050](#) Single Snap Fastener (Snaps installed on long side of mat)

#### Table Roll Item Numbers with Hardware

Size	Blue	Brown	Gray
2' x 24' (0.6 m x 7.3 m)	<a href="#">8264</a>	<a href="#">8261</a>	<a href="#">8263</a>
4' x 24' (1.2 m x 7.3m)	<a href="#">8254</a>	<a href="#">8251</a>	<a href="#">8253</a>

#### Table Roll Includes:

- 2 [3040](#) 15' (4.6 m) Ground Cords
- 2 [3050](#) Single Snap Fastener (not installed)

#### Table Roll Item Numbers without Hardware

Size	Blue	Brown	Gray	Dark Blue
2' x 50' (0.6 m x 15.2 m)	<a href="#">8234</a>	<a href="#">8231</a>	<a href="#">8233</a>	<a href="#">8245</a>
2.5' x 50' (0.8 m x 15.2 m)	<a href="#">8244</a>	<a href="#">8241</a>	<a href="#">8243</a>	<a href="#">8246</a>
3' x 50' (0.8 m x 15.2 m)	<a href="#">8274</a>	<a href="#">8271</a>	<a href="#">8273</a>	<a href="#">8247</a>
4' x 50' (1.2 m x 15.2 m)	<a href="#">82A4</a>	<a href="#">82A1</a>	<a href="#">82A3</a>	

#### 8200 SERIES DISSIPATIVE VINYL THREE-LAYER MATS AND ROLLS

926 JR Industrial Drive, Sanford, NC 27332  
 WEB SITE: [StaticControl.com](https://www.StaticControl.com)  
 PHONE (919) 718-0000 | WEST: (909) 627-9634

**DRAWING  
NUMBER**  
8200 Series

**DATE**  
October  
2022

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Desco:

[8214](#) [8264](#) [8211](#) [8203](#) [8254](#) [8261](#) [8263](#) [8233](#) [82A4](#) [8274](#) [8273](#) [8244](#) [8231](#) [8234](#) [8213](#) [82A3](#) [8204](#)

## SCS:

[8201](#) [8281](#) [8283](#) [8284](#) [8293](#) [8251](#) [8253](#) [8291](#) [8294](#) [8243](#) [8223](#) [8271](#) [8224](#) [8241](#) [8213 \(GRAY 2'X4'\)](#) [8221](#)