

## 3M™ Surface Resistance Meter 625

The Surface Resistance Meter 625 is a wide range, multi-scale, auto-ranging meter. The meter is appropriate for auditing static control work surfaces. The meter is battery powered and simple to use.

Useful for audit testing required by ANSI/ESD S-20.20 and EIA 625.




3M™ Surface Resistance Meter 625  
Includes: Meter, case, cable and instructions.

### Specifications

Electrical	Typical Value
Measurement	10 <sup>3</sup> to 10 <sup>12</sup> ohms/square ASTM D257
Resolution	one order of magnitude
Accuracy	± 1/2 decade
Power	9 volt battery
Electrodes	Parallel Bar
Mechanical	
Weight	4 oz
Size	5.1 in. x 2.8 in. x 1.1 in. (130 mm x 72 mm x 27 mm)
Part Numbers	

SRMETER 625

Surface Resistance/Resistivity RTG Meter



## 3M™ Surface Resistance Meter 625

3M is a trademark of 3M Company.

### Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.



### Electronics Materials Solutions Division Static Control Products

926 JR Industrial Drive  
Sanford, NC 27332-9733  
Toll-Free: 866-722-3736  
International: 919-718-0000  
Email: 3mstaticinfo@mmm.com  
www.3Mstatic.com

Please recycle. Printed in USA.  
© 3M 2014. All rights reserved.  
78-9102-1939-9 JHA

### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for one year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SCS:

SRMETER