


# OIL TIGHT Miniature Incandescent Indicators


FOR MOUNTING IN 11/16" CLEARANCE HOLE



T-3 1/4  
MINIATURE  
BAYONET BASE

See lamp ratings  
on page K.

Recognized under the component  
program of Underwriters'  
Laboratories Inc.



123-1310-1231-403  
Dome lens

For materials and finishes of products  
in this group, see preceding page.

## 123 SERIES


BASE PART NUMBERS

screw terminals	soldering terminals	quick connect terminals
123-1310-12-103	123-0410-12-103	123-5710-12-103

CAP PART NUMBERS

COMPLETE ASSEMBLY PART NUMBERS

<p><b>DOMES</b></p> <p>123-1211-403 back frosted</p> <p>123-1231-403 unfrosted</p>	123-1310-1211-403	123-0410-1211-403	123-5710-1211-403
	123-1310-1231-403	123-0410-1231-403	123-5710-1231-403



218-0410-0131-403  
Convex lens with inserted film disc

## 218 SERIES 124 SERIES

BASE PART NUMBERS

screw terminals	soldering terminals	quick connect terminals
124-1310-01-103	124-0410-01-103	124-5710-01-103

CAP PART NUMBERS

COMPLETE ASSEMBLY PART NUMBERS

<p><b>CONVEX</b></p> <p>† 218-0131-403 unfrosted (with disc)</p> <p>124-0111-403 back frosted (without disc)</p>	† 218-1310-0131-403	† 218-0410-0131-403	† 218-5710-0131-403
	124-1310-0111-403	124-0410-0111-403	124-5710-0111-403

† See "Legend Film Discs" on page 1E.

Part numbers listed in this catalog designate products with RED lens.  
For ordering lens colors other than red, consult chart on page 1E.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Dialight:

[124-0136-403](#) [123-1211-203](#) [123-1233-403](#) [124-0410-01-103](#) [123-1233-303](#) [123-1310-12-203](#) [123-1310-12-103](#)  
[124-0111-203](#) [124-0410-01-203](#) [124-0113-403](#) [124-0131-403](#) [123-1211-403](#) [123-1235-403](#) [124-1363-01-113](#) [124-](#)  
[0111-403](#) [123-0410-12-103](#) [123-1232-403](#) [123-1231-303](#) [124-1310-01-103](#) [124-0131-203](#) [124-0135-403](#) [123-0410-](#)  
[12-203](#) [123-1231-203](#) [123-1212-203](#) [123-1234-403](#) [124-1310-01-203](#) [123-1213-203](#) [123-1213-403](#) [124-0133-403](#)  
[124-0132-403](#) [123-5710-12-103](#) [123-1237-403](#) [123-1231-403](#) [124-5710-01-103](#)