



**07452 SHOP TRAVELER
HAS POCKET**

RoHS and REACH Compliance Statement

None of the RoHS restricted materials or REACH substances of very high concern are intentionally added in manufacturing this product. Ref: Directive 2002/95/EC Article 4.1. and Regulation (EC) No. 1907/2006. See Desco Industries Inc. Limited Warranty at Desco.com.

"It should be understood that any object, item, material or person could be a source of static electricity in the work environment. Removal of unnecessary nonconductors, replacing nonconductive materials with dissipative or conductive materials and grounding all conductors are the principle methods of controlling static electricity in the workplace, regardless of the activity."
[ESD Handbook ESD TR.20.20-2008 section 2.4 Sources of Static Electricity]

Product over one year old should be evaluated by the user to determine acceptability for the user's application. Desco Industries, Inc. recommends those tracking useful life of product to use shipping/invoice date as Desco Industries, Inc. expressly warrants that for a period of one (1) year from the date of purchase, our Desco Shop Traveler will be free of defects in material (parts) and workmanship (labor). See details of Limited Warranty online at Desco.com/Warranty.aspx.

Description:

Desco's static safe shop travelers are made from standard weight 0.003" thick (3 mil) polyester/polyolefin laminated structure. They are designed for top loading standard A size (8.5" x 11") sheets of paper with an additional 8.5" x 10" pocket.

Electrical Properties:

Static Decay:	< 3.0 sec.	per IEC 61340-5-1 1988 method B.2
Surface Resistance:	10E10 ohms	per ANSI/ESD S4.1

Specifications:

Polycarbonate Compatibility:	3,400 PSI @ 73°F	
Corrosivity:	Negligible	per FTMS 101C-3005
Tensile Strength:	2000-3000 PSI	per ASTM D-882
Elongation @ Break:	500-800%	per ASTM D882
Ball Burst Impact Strength:	20-30 cm/kg	per ASTM D-3420
Tear Propagation:	200 grams	per ASTM D-1938
Modulus of Elasticity:	10,000-15,000 PSI	per ASTM D-882A
Coefficient of Friction:	0.3 Kinetic, Film to Film	per ASTM D-1894

Chemical Properties:

Corrosion	No effect on aluminum, copper, silver, Sn-Pb coated foil, stainless steel, low carbon steel
Polycarbonate Compatible	Yes
Amines or N-Octanoic Acid	Not present
Humidity independent	
Has no measurable outgassing.	

Hot stamped with:

DESCO STATIC SAFE SHOP TRAVELER ITEM #07452



Made in the
United States of America

*Specifications and procedures subject to change without notice.
Tolerance if not otherwise specified ± 10%*

SHOP TRAVELER, WITH POCKET, 3 MIL, PACK OF 25

DESCO

DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE:
Desco.com
PHONE (909) 627-8178
DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407
PHONE (781) 821-8370 FAX (781) 575-0172

DRAWING NUMBER
07452

DATE:
January
2012

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Desco:

07452