


# Large Incandescent Indicators

FOR MOUNTING IN 1" CLEARANCE HOLE  
FOR 6 TO 32V OPERATION




G-6  
DOUBLE CONTACT  
BAYONET BASE

See lamp ratings  
on page K.

These series indicator lights meet or exceed requirements of MIL-L-3661.

For materials and finishes of products in this group, see page 38D.

Recognized under the component  
program of Underwriters'  
Laboratories Inc.  
75W., 125V.



51-3204-0111-301  
Convex lens

## WITH SCREW-ON LENS CAPS

### 51 SERIES

#### BASE PART NUMBERS

fixed solder	fixed screw
51-3406-01-301	51-3206-01-301

#### CAP PART NUMBERS

#### COMPLETE ASSEMBLY PART NUMBERS

<p><b>CONVEX</b> 51-0111-300 back frosted 51-0131-300 unfrosted</p>	<p>51-3404-0111-301 51-3404-0131-301</p>	<p>51-3204-0111-301 51-3204-0131-301</p>
<p><b>FLAT</b> 51-0211-300 back frosted 51-0231-300 unfrosted</p> <p>For legends on flat faced lens, see page P.</p>	<p>51-3404-0211-301 51-3404-0231-301</p>	<p>51-3204-0211-301 51-3204-0231-301</p>
<p><b>FACETED</b> 51-0431-300 unfrosted</p>	<p>51-3404-0431-301</p>	<p>51-3204-0431-301</p>

Part numbers shown in gray are normally  
in inventory at your Dialight Distributor.

Part numbers listed in this catalog designate products with RED lens.  
For ordering lens colors other than red, consult chart on page 2D.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Dialight:

[051-0135-303](#) [051-0432-303](#) [051-3206-01-303](#) [051-3202-01-300](#) [051-3402-01-301](#) [103-0533-403](#) [103-1211-403](#)  
[103-1335-403](#) [103-1236-403](#) [103-0511-403](#) [051-0133-203](#) [051-0131-203](#) [051-3202-01-301](#) [103-1336-403](#) [051-](#)  
[0111-303](#) [051-0132-203](#) [051-3402-01-303](#) [051-0117-203](#) [051-0114-203](#) [103-1235-403](#) [103-1212-403](#) [103-0531-203](#)  
[051-3206-01-300](#) [051-3402-01-300](#) [051-3406-01-300](#) [103-1333-403](#) [103-1233-403](#) [103-1310-05-103](#) [051-3206-01-](#)  
[301](#) [051-3202-01-303](#) [051-3406-01-301](#) [103-0512-403](#) [103-0536-403](#) [103-1232-403](#) [103-1332-403](#) [103-1331-403](#)  
[103-1231-403](#) [103-0531-403](#) [051-3202-01-203](#) [103-1214-403](#) [103-1237-403](#) [103-1337-403](#) [103-0513-403](#) [103-](#)  
[1213-403](#) [103-1216-403](#) [051-0112-303](#) [051-0113-303](#) [103-1217-403](#) [051-0431-303](#) [103-1334-403](#) [103-1234-403](#)  
[031-0232-300](#) [051-0137-303](#) [051-0437-303](#) [051-3206-01-203](#) [051-3206-01-807](#)