

554 SERIES SINGLE AND DUAL LAMP SWITCHESCaps Ordered Separately
See Page 27.

MOMENTARY ACTION 0.5 TO 7 AMP , 30VDC OR 125VAC (MAX)

PART NO.	ACCEPTS CAP SIZE	CONTACT CIRCUIT	FIG
554-1121	ALL	SPDT	1
554-1121-111	1/2" SQ.	SPDT	2
554-1121-211	5/8" SQ.	SPDT	3
554-1121-311	5/8" X 3/4"	SPDT	4
554-1121-411	3/4" SQ.	SPDT	5
554-1121-511	3/4" X 1"	SPDT	6
554-1221	ALL	DPDT	1
554-1221-111	1/2" SQ.	DPDT	2
554-1221-211	5/8" SQ.	DPDT	3
554-1221-311	5/8" X 3/4"	DPDT	4
554-1221-411	3/4" SQ.	DPDT	5
554-1221-511	3/4" X 1"	DPDT	6
554-5121-411	DUAL LAMP	SPDT	7
554-5221-411	DUAL LAMP	DPDT	7

MOMENTARY ACTION .015 TO 1 AMP , 30 VDC OR 125VAC (MAX)

PART NO.	ACCEPTS CAP SIZE	CONTACT CIRCUIT	FIG
554-2121	ALL	SPDT	1
554-2121-211	5/8" SQ.	SPDT	3
554-2121-411	3/4" SQ.	SPDT	5
554-2221	ALL	DPDT	1
554-2221-111	1/2" SQ.	DPDT	2
554-2221-211	5/8" SQ.	DPDT	3
554-2221-311	5/8" X 3/4"	DPDT	4
554-2221-411	3/4" SQ.	DPDT	5
554-2221-511	3/4" X 1"	DPDT	6
554-6221-411	DUAL LAMP	DPDT	7

MOMENTARY ACTION, 1 TO 50 mA, 30VDC (MAX)

PART NO.	ACCEPTS CAP SIZE	CONTACT CIRCUIT	FIG
554-3121	ALL	SPDT	1
554-3221	ALL	DPDT	1
554-3221-211	5/8" SQ.	DPDT	2

ALTERNATE ACTION 0.5 TO 7 AMP, 30VDC OR 125 VAC (MAX)

PART NO.	ACCEPTS CAP SIZE	CONTACT CIRCUIT	FIG
554-1131-211	5/8" SQ.	SPDT	3
554-1131-411	3/4" SQ.	SPDT	5
554-1131-511	3/4" X 1"	SPDT	6
554-1231	ALL	DPDT	1
554-1231-111	1/2" SQ.	DPDT	2
554-1231-211	5/8" SQ.	DPDT	3
554-1231-311	5/8" X 3/4"	DPDT	4
554-1231-411	3/4" SQ.	DPDT	5
554-1231-511	3/4" X 1"	DPDT	6


ALTERNATE ACTION, .015 TO 1 AMP, 30VDC OR 125VAC (MAX)

PART NO.	ACCEPTS CAP SIZE	CONTACT CIRCUIT	FIG
554-2231-111	1/2" SQ.	DPDT	2
554-2231-211	5/8" SQ.	DPDT	3
554-2231-311	5/8" X 3/4"	DPDT	4
554-2231-411	3/4" SQ.	DPDT	5
554-2231-511	3/4" X 1"	DPDT	6
554-6231-411	DUAL LAMP	DPDT	7

Material & Finish: All plastic switch components made from 94V-0 Material

Neon and incandescent lamp information on Pages 35 and 36.

Dimensions in mm [inches]



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[554-1121-111](#) [554-1231-411](#) [554-1121-511](#) [554-1121-311](#) [554-1231-311](#) [554-2221-411](#) [554-1131-211](#) [554-2231-211](#) [554-2231-111](#) [554-2221-211](#) [554-2121-411](#) [554-1221](#) [554-1231](#) [554-2221](#) [554-1121-411](#) [554-1121](#) [554-1221-511](#) [554-1131-411](#)