

3M™ Electronics Vacuums 497AJW, 497AJK

The Small Particle Collection Vacuum 497AJW is designed for small particle collection. Portability, quick setup and efficient safe operation are key features of this vacuum. It contains a one horsepower, six amp motor. The Small Particle Collection Vacuum 497AJW comes with a Type 2 Filter, a detachable cord and plastic hose (approximately 7 feet). The 3M™ Small Particle Collection Filter FF1 includes a single-use disposable filter, storage bag and end cap (ordered separately).

- Features:
- Detachable power cord for easy storage
 - Lightweight and easy to setup
 - Includes 7 ft. hose and 15 ft. power cord
 - Dimensions: 7.8 in. x 17.8 in. x 9.3 in.



3M™ Small Particle Collection Vacuum 497AJW

Property	Typical Value	Test Method
Model 497AJW	120VAC, 50/60 Hz, 6.0 amps	Supplier
Model 497AJK	120VAC, 50/60 Hz, 6.0 amps	Supplier
Dimensions		
Length	17.8 inches (45.2 cm)	3M Internal
Width	7.8 inches (19.7 cm)	3M Internal
Height	9.3 inches (23.5 cm)	3M Internal
Weight	11 lbs.	3M Internal
Sound pressure Level	74.0 dBA	ISO Standard 11201; 1st edition 1995-12-15
Motor	1 HP	

Thermally protected with automatic reset.

Small Particle Collection 497AJW comes complete with:

- Hose, 7 ft SV-SH20 – 78-8095-4393-3
- Power Cord SV-PC15 - 78-8079-9531-7
- Small Particle Collection Filter FF1 - 78-8079-9484-9 (ordered separately, includes filter, storage bag and end cap)

3M™ HEPA Vacuum 497AJK comes complete with:

- Hose, 32 in. - 78-8063-1848-7
- Power Cord, 8 ft. SV-PC8 - 80-6104-7964-6
- Crevice Nozzle SV-CN1 - 80-6104-7958-8
- Crevice Brush SV-SB1 - 80-6104-7957-0
- Shoulder Strap SV-CS1 - 80-6104-7959-6
- HEPA Curved Wand Nozzle - 78-8063-1847-9

Product Data Sheet

3M™ Electronics Vacuums 497AJW, 497AJK

The 3M™ HEPA Vacuum 497AJK is designed for clean-up of hazardous material. Portability, quick setup and efficient safe operation are key features of this vacuum. It comes complete with a HEPA filter, detachable power cord, specialized stretch hose and nozzle and curved wand nozzle.

Features:






- Detachable power cord for easy storage
- Attachments that quickly dissipate static charge
- Lightweight and easy to set up
- Complete attachment offering including: power cord, specialized stretch hose and nozzle and curved wand nozzle
- Dimensions: 7.8 in. x 17.8 in. x 9.3 in.



Product Data Sheet

3M™ Electronics Vacuum 497AJW, 497AJK Replacement Parts and Accessories

Image	Part No.	Description
	SV-MPF2	High Performance Filter, Type 2 for medium particles. Specifically designed for collecting unwanted toner from copiers and laser printers.
	SV-SPF1	Fine Particle Filter, Type 1. This filter has a more concentrated weave for collecting extremely fine particles.
	SV-CS1	Carrying Strap Assembly
	SV-SH32	Vacuum Hose Assembly. This 32 inch hose stretches to approximately 10 feet.
	SV-LRP	Long Red Filter Plug. This plug is used to cover the filter inlet for storage when the vacuum cleaner is not in use.
	SV-SRP	Short Red Filter Plug. This plug is used to cover the filter inlet for disposal.

Image	Part No.	Description
	SV-CN1	Crevice Nozzle
	SV-CB1	Crevice Brush
	SV-WA2	Curved Wand Nozzle
	SV-NN	Needle Nose Nozzle
	SV-DBSD1	Dusting Brush

Product Data Sheet

3M™ Electronics Vacuum 497AJW, 497AJK

3M is a trademark of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for three years from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electronics Materials Solutions Division Static Control Products

926 JR Industrial Drive
Sanford, NC 27332-9733
Toll-Free: 866-722-3736
International: 919-718-0000
Email: 3mstaticinfo@mmm.com
www.3Mstatic.com

Printed in USA.
© 3M 2014. All rights reserved.
78-9102-1936-5 JHA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Desco:

[SV-NN](#) [SV-WA2](#)

SCS:

[SV-PCR3](#) [SV-DBSNAP](#)