

3M™ Wrist Strap – Adjustable Elastic Fabric

This standard performance wrist strap set features a fully adjustable stretch fabric wrist band and coiled cord. The band provides 360 degree conductivity around the wrist for maximum skin contact. Band curling is reduced by the woven band fabric. The retractable coil cord connects to the wrist band via a 4mm post snap and contains a 1 megohm resistor. Includes alligator clip. Band available in blue or maroon.



3M™ Wrist Strap MWS61M



3M™ Wrist Strap BLUEWS61M

**WARNING:**
All 3M Wrist Straps should not be used in areas where the individual may come in contact with electrical circuitry exceeding 250 volts.

Specifications - Band

Fabric	Elastic nylon with conductive threads
Color	Blue or maroon
Snap	4mm

Specifications - Cord

Resistance	1 megohm
Color	Black
Length	6 or 12 feet extended
Flex Life	≥ 16,000 flexes
Banana Plug	Spinning
Snap	4mm

Part Numbers 4mm (1/8") snap

BLUEWS	Blue Adjustable Fabric Wristband
BLUEWS61M	Blue Adjustable Fabric Wristband and 6 ft cord
BLUEWS121M	Blue Adjustable Fabric Wristband and 12 ft cord
MWS	Maroon Adjustable Fabric Wristband
MWS61M	Maroon Adjustable Fabric Wristband and 6 ft cord
MWS121M	Maroon Adjustable Fabric Wristband and 12 ft cord
BLCC61M	6 ft cord
BLCC121M	12 ft cord

Meets the requirements of EIA 625.

3M™ Wrist Strap – Adjustable Elastic Fabric

3M is a trademark of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for one year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electronics Materials Solutions Division Static Control Products

926 JR Industrial Drive
Sanford, NC 27332-9733
Toll-Free: 866-722-3736
International: 919-718-0000
Email: 3mstaticinfo@mmm.com
www.3Mstatic.com

Please recycle. Printed in USA.
© 3M 2014. All rights reserved.
78-9102-1671-8 JHA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SCS:

[BLCC61M](#) [MWS121M](#) [BLUEWS121M](#) [BLUEWS](#) [MWS](#) [BLCC121M](#)