

M5GO3 Bottom

SKU:A014-D



Description

As the third generation of M5GO Bottom, M5GO3 Bottom is tailored for M5CoreS3. This model not only integrates functions such as infrared transmission LED, 500mAh lithium battery, and RGB lights but also is compatible with LEGO bricks, providing more possibilities for CoreS3 applications.

M5GO3 Bottom base has two sets of HY2.0-4P expansion interfaces, which bring out commonly used ADC/DAC/UART pins, making it convenient for various types of sensors to be connected. Whether it's temperature, humidity, light, or other types of sensors, users can easily connect them to the base.

The bottom of the base adopts pogo pin magnetic charging interface. When attached to the charging base, the current will safely flow into the internal battery through the built-in TP4057 charging chip, providing charging function for the base. In addition, the pogo pin interface also extends the main control I2C bus, making it convenient for external expansion through magnetic adsorption.

M5GO3 Bottom base also has built-in magnetic absorption and is designed with LEGO-compatible holes on the back, which means it can seamlessly connect with other LEGO structural designs, enabling more creative shapes. On both sides of the M5GO3 Bottom base, there are 10 programmable RGB lights (SK6812), combined with frosted light-shielding strips, creating a soft and comfortable lighting effect. Users can control the

brightness and color of these lights through programming, adding more fun to their projects.

Features

- Compatible with M5CoreS3
- Infrared transmitter
- Programmable LED strip
- 500mAh lithium battery
- HY2.0-4P Expands the interface
- Compatible with Lego building structure
- Suitable for magnetic charging base

Includes

- 1x M5GO3 Bottom
- 2x M3*16 screws
- 2x M3*18 screws


Applications

- CoreS3 Extension
- IOT Project
- STEAM Education

Specification

Resources	Parameters
RGB	10*WS2812
Battery	3.7V@500mAh
Product Size	54*54*15mm
Package Size	136* 92*20mm

Product Weight	30.3g
Package Weight	43.3g



Products related to this item

[M5GO BOTTOM2 \(A014-C\)](#)

[M5GO BOTTOM \(A014\)](#)


[CoreS3 \(K128\)](#)

Related Link


[TP4057](#)

Schematic


RGB LED * 10




Socket




Power



IR



M5Bus



PinMap

CoreS3	G5	G7		
WS2812	RGB			
IR		IR		

CoreS3	GND	VCC	G9	G8
PORT B (BLACK)	GND	5V	IN	OUT

CoreS3	GND	VCC	G17	G18
PORT C (BLUE)	GND	5V	TXD	RXD

CoreS3	GND	VCC	G12	G11
POGO	GND	5V	SDA	SCL

Module Size



COMPARE	CORE	RGB	IMU	IR	BATTERY	MIC
M5G0 BOTTOM	BASIC (CORE)	10*SK6812	/	IR	500mAh	SPQ2410
M5G02 BOTTOM	CORE2	10*SK6812	MPU6886	/	500mAh	SPM1423
M5G03 BOTTOM	CORES3	10*WS2812	/	IR	500mAh	/

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[M5Stack:](#)

[A014-D](#)