

LC SERIES

CONSTANT CURRENT LED DRIVERS

CONSTANT CURRENT LED DRIVER CASE STYLE D: METAL



GENERAL INFORMATION

LED Drive Type	Constant Current Class 2
Maximum Wattage	16W
Input Voltage	120VAC (+/-10%) or 120-277VAC (+/-10%)
Input Frequency	50/60Hz
Power Factor @ Full Load	>0.9
Efficiency @ Full Load	Up to 83% (See Chart Below)
THD	<20%
Start-Up Time	<750ms
Output Current Tolerance	5%
Line Regulation	1%
Load Regulation (Max Load)	2%
Dimming	Phase or Non-dimming
Output Over Current Protection	Hiccup Mode
Output Short-Circuit Protection	Hiccup Mode
Over Temperature Protection	Hiccup Mode
EMI Compliance	FCC Part 15 Class B

ENVIRONMENTAL SPECIFICATIONS

Minimum Operating Temp.	-40° C
Maximum Case Temp.	+90° C
Maximum Storage Temp.	+85° C
Maximum Relative Humidity	95% Non-condensing
Transient Protection	2kV L-N, 4kV L/N-GND
UL Environment Rating	Dry and Damp
Sound Rating	Class A

APPROVALS



WARRANTY

- 5 year limited warranty

ELECTRICAL SPECIFICATIONS


Max. Power	Rated Current	Output Voltage (VDC)	Input Voltage	Dimming Type	Input Power	Input Current	Efficiency	Part Number
16W	Non-Dimming							
	500mA	10 - 32 VDC	120 - 277 VAC	Non-Dimming	20W	0.19/0.09A	83%	LC16-0500N-UNV-D
	Dimming							
	350mA	15 - 46 VDC	120 VAC	Phase Dimming	20W	0.18A	81%	LC16-0350P-120-D
	700mA	8 - 23 VDC						LC16-0700P-120-D

Custom output current available on Made to Order basis

LC SERIES

CONSTANT CURRENT LED DRIVERS

SIZING INFORMATION: CASE STYLE D



Specifications subject to change without notice.

WIRING INFORMATION



Input	12", Black (L), White (N) #18AWG
Output	12", Red (+), Blue (-) #18AWG

PACKAGING INFORMATION

Package Weight	8.3oz
Quantity	60pcs/carton

PERFORMANCE CURVES

Efficiency Vs. Output Power





LC SERIES


CONSTANT CURRENT LED DRIVERS

PERFORMANCE CURVES


Power Factor Vs. Output Power



Dimming Curve



Lifetime Vs. Case Temperature



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hatch Lighting:](#)

[LC16-0350P-120-D](#) [LC16-0700P-120-D](#)