


# OIL TIGHT Large Incandescent Indicators

FOR MOUNTING IN 1" CLEARANCE HOLE



S-6  
DOUBLE CONTACT  
BAYONET BASE

See lamp ratings  
on page K.

Recognized under the component  
program of Underwriters'  
Laboratories Inc.



103-3502-1331-403  
Torpedo Faceted lens

For materials and finishes of products  
in this group, see preceding page.

☐ **MOVABLE TERMINALS:** Terminal  
part makes direct contact to lamp,  
no current is carried by springs.  
Wiring is displaced only 1/16" on  
insertion of lamp.

☐ **FIXED TERMINALS:** Connecting  
wiring may be rigid. No terminal  
movement during insertion of lamp.

## 103 SERIES

### BASE PART NUMBERS

movable screw terminals	fixed screw terminals	fixed soldering terminals
<p>1/16 PANEL (REF.) 1/16 X 1-1/8 ACROSS FLATS HEX. NUT. 1-27 NS THD. MOUNTING BUSHING 5/64 X 1-3/16 O.D. FLANGE 1-7/8 MAX. PROJECTION BACK OF PANEL 6-32 NC THD.</p>	<p>6-32 NC THD.</p>	<p>3/32 DIA. (2 HOLES)</p>
103-3502-05-103	103-3202-05-103	103-3402-05-103

### CAP PART NUMBERS

### COMPLETE ASSEMBLY PART NUMBERS

CAP PART NUMBERS	COMPLETE ASSEMBLY PART NUMBERS		
<p><b>TORPEDO</b> 103-0531-403 unfrosted 103-0511-403 back frosted</p>	103-3502-0531-403	103-3202-0531-403	103-3402-0531-403
	103-3502-0511-403	103-3202-0511-403	103-3402-0511-403
<p><b>TORPEDO FACETED</b> 103-1331-403 unfrosted</p>	103-3502-1331-403	103-3202-1331-403	103-3402-1331-403
<p><b>DOME</b> 103-1231-403 unfrosted 103-1211-403 back frosted</p>	103-3502-1231-403	103-3202-1231-403	103-3402-1231-403
	103-3502-1211-403	103-3202-1211-403	103-3402-1211-403

☐ For movable soldering terminals, change the group of  
digits of the part number that reads -3502- to -3602-.  
Example: 103-3602-0531-403.

Part numbers shown in gray are normally  
in inventory at your Dialight Distributor.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[103-3402-05-103](#) [103-3202-05-103](#)