



Important notes about Classic Panel Mount Indicator Catalog Pages

SCROLL DOWN TO VIEW CATALOG PAGE

This catalog page is out-of-print and is used with the understanding that the information shown could be out-of-date. In many cases, part numbers shown on this page are discontinued. Most notably, many “Complete Assembly” parts, which consist of a cap and a base, can no longer be ordered by the 14-digit ordering code. To obtain these parts, please order the cap and base part numbers separately. This process provides the components contained with the original “Complete Assembly” part number.

All Dialight Classic Panel Mount Indicators need a leading 3-digit numerical series. In some cases, this catalog will show a 2-digit series. In this case, please add a leading zero. For example, 81-0211-300 becomes 081-0211-300.

Part numbers listed on Dialight catalog pages designate parts with Red lenses. For ordering lens colors other than red, consult the chart below. In most cases, the color is dictated by the 7th digit. For example, 095-0932-003 for a green cap.

Lens Colors	
1 - Red	5 - White
2 - Green	6 - Light Yellow
3 - Yellow	7 - Clear
4 - Blue	


[Click here for a cross reference guide to assembly part numbers.](#)

[Click here to view Frequently Asked Questions concerning Panel Mount Indicators.](#)

SCROLL DOWN TO VIEW CATALOG PAGE

Large Incandescent Indicators

WITH LIGHT SHIELD LENS CAPS
FOR MOUNTING IN 1" CLEARANCE HOLE
FOR 6 TO 250V OPERATION




S-6
CANDELABRA
SCREW BASE

See lamp ratings
on page K.

Recognized under the component
program of Underwriters'
Laboratories Inc.
75W., 125V.

MATERIALS AND FINISHES:

- **Mounting Bushing:** Standard—brass, white nickel finish. Optional—black nickel finish.
- **Light Shield Cap:** Brass, polished chrome finish. Optional—black nickel finish.
- **Knurled Flange Ring:** Standard—brass, polished chrome finish. Optional—black nickel finish.
- **Internal-tooth Lockwasher:** Phosphor bronze, white nickel finish.
- **Terminals:** Solder — brass, hot tinned. Screw—brass, white nickel finish.
- **Quick Connect—**brass, tinned. Mate with standard female receptacles.
- **Mounting Nut:** Brass, white nickel finish.



151-4001-2900-301

47 SERIES
49 SERIES
50 SERIES
151 SERIES

WITH SCREW- ON LENS CAPS

solder terminal	screw terminal (protruding pos.)	quick connect terminal
47-4001-29-301	47-3101-29-301	47-6701-29-301

BASE PART NUMBERS

CAP PART NUMBERS	COMPLETE ASSEMBLY PART NUMBERS		
<p>DOME 47-2900-300 one opening, 3/8"x1"</p>	47-4001-2900-301	47-3101-2900-301	47-6701-2900-301
<p>DOME 49-2900-300 one opening, 1/4"x1"</p>	49-4001-2900-301	49-3101-2900-301	49-6701-2900-301
<p>DOME 50-2900-300 one opening, 1/8"x1"</p>	50-4001-2900-301	50-3101-2900-301	50-6701-2900-301
<p>DOME 151-2900-300 one opening, 9/16"x1"</p>	151-4001-2900-301	151-3101-2900-301	151-6701-2900-301

Part numbers shown in gray are normally
in inventory at your Dialight Distributor.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight:

[047-4001-29-301](#) [047-2900-300](#) [047-3101-29-300](#) [047-2900-200](#) [047-2900-400](#) [049-2900-300](#) [047-3101-29-301](#)
[047-4001-29-300](#) [047-6701-29-300](#) [151-2900-300](#) [049-2900-200](#) [151-2900-200](#) [047-6701-29-301](#)