



## Mike 3A

Weather Resistant GPS Magnetic Mount Antenna



### Key Features

- 28dB LNA gain
- Weather Resistant
- Dual mount
- Ground plane independent

### General Description

The Mike 3A is a compact dual mount GPS antenna, tuned to 1575.42MHz.

Dual mounting: with its magnetic base and separate adhesive pad, the Mike 3A can be mounted onto a diverse range of surfaces.

The weather resistant design, equivalent to IP66, make it an ideal outdoor GPS antenna that can be used for a host of different GPS applications including: vehicle/fleet/asset tracking and mobile applications.

The built in Low Noise Amplifier (LNA) provides a 28dB gain producing stronger signals which reduce satellite fix times.

### Additional Considerations

- Improves signal to noise ratio for mobile applications
- Mixed mounting - magnetic or adhesive pad
- Meets all EU compliance criteria for electronic goods





## Mike 3A

Weather Resistant GPS Magnetic Mount Antenna

### Dielectric Antenna

VSWR:	1.5:1
Impedance:	50 Ohm
Peak Gain:	>3dBic (Based on 7 x 7cm Ground plane)
Gain Coverage:	>4dBic at 90°
Polarization:	RHCP

### Mechanical Specifications

Dimensions:	L48.5 x W36.5 x H16.5mm
Cable:	RG174
Connector:	SMA Male
Mounting Method:	Magnetic


### GPS Antenna

LNA Gain:	28dB Typical
Noise Figure:	1.5dB
Connector:	SMA Male
VSWR:	<2.0
DC Voltage:	3.0V - 5.0V
DC Current:	10mA Max

### Environmental Specifications

Operating Temperature:	-40 - +85°C
Storage Temperature:	-45 - +100°C
Humidity:	95% - 100% RH
Mounting method:	Magnetic

### VSWR







## Mike 3A

Weather Resistant GPS Magnetic Mount Antenna

### Return Loss



### Radiation Patterns







## Mike 3A

Weather Resistant GPS Magnetic Mount Antenna

### Radiation Patterns



### Ordering Details

Part Number	Description
MIKE3A/2.5M/SMAM/S/S/17	GPS, IP67 Magnetic Mount Antenna 2.5m Cable SMA Male Connector
MIKE3A/3M/SMAM/S/S/17	GPS, IP67 Magnetic Mount Antenna 3m Cable SMA Male Connector
MIKE3A/5M/SMAM/S/S/17	GPS, IP67 Magnetic Mount Antenna 5m Cable SMA Male Connector

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siretta:

[MIKE3A/0.5M/SMAM/RA/S/17](#) [MIKE3A/2.5M/SMAM/S/S/17](#) [MIKE3A/5M/SMAM/S/RA/17](#) [MIKE3A/5M/SMAM/S/S/17](#)