

	1	2	3	4	5	6	7	8	9	10		
A	ebn-papst MFG. NOTES						REV. EC # REVISION DESCRIPTION		DATE	D.ENG.	CHECKER	
	1 LEAD DIMENSION IS AT FULL EXTENSION						001 2887 RELEASE TO PRODUCTION		06/08/00	BARB	MZ	
							002 6579 CHANGE 22AWG TO 18AWG. ADD PROD.ID LABEL		09/22/04	DTM	DW	
							003 6579 CHANGE LEAD LENGTH TO 72" (WAS 36")		08/05/16	DTM	DTM	
B												B
C												C
D												D
E												E
F												F
G												G
H												H
												H
												H
												H

6

1

605-50-2660

PRODUCT ID LABEL

5

1

400-50-0003

WIRE TIE 4"

4

1

410-18-0003

GREEN/YELLOW AWG18 UL1007

3

2

410-18-0014

BLACK AWG18 UL1007

2

3

405-12-0089

AMP 350536-1 TERM (REEL)

REF

405-12-0006

AMP 350550-1 TERM (LOOSE)

1

1

405-14-0004

AMP 350766-1 CONNECTOR

ITEM

QTY

PART NUMBER

DESCRIPTION

ebn-papst Inc. DISCLOSURE		MATERIAL: N/A		BEND DEDUCTION N/A		PART NO. 420-05-0276		ebmpapst	
THIS DOCUMENT IS THE PROPERTY OF ebn-papst Inc. ITS USE IS AUTHORIZED BY ebn-papst Inc. ONLY. ALL QUESTIONS MUST BE REFERRED TO ebn-papst Inc. PERSONNEL: DESIGN ENG., MFG.ENG., AND / OR PURCHASING. CAUTION: ANY PRINTED COPY IS UNCONTROLLED AND TO BE USED FOR REFERENCE ONLY. REFER TO ebn-papst Inc. CAD SYS. FOR VERIFICATION.		FINISH: N/A		COSMETICS PER ebn-papst SPEC-Q-1		TITLE AC POWER CONTROL HARNESS			
		IF APPLICABLE PLACE SECOND FINISH AND DESCRIPTION HERE		SEE CAD FOR DIMS. NOT SHOWN		FIRST USED ON 420-05-0276			
		ALL INNER BEND RADII = 1mm BOTTOM BEND UNLESS OTHERWISE STATED		BREAK ALL SHARP EDGES					
		TOLERANCES, UNLESS OTHERWISE STATED:		ALL DIMENSIONS ARE IN INCHES					
DECIMAL .XXX ± .020		HOLES .XXX ± .003		TOLERANCES FOR CNC FLAT .XXX		DESIGN ENG. DTM		ORIG. DATE 05/01/00	
TOLERANCE .XX ± .030		ANGLES ± 1° REF		EXCLUDING HOLE DIA. +/- .010		E# EA-0663		REVISION 003	
Form No. 1073 Rev. H								SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ebm-papst:](#)

[420-05-0276](#)