





| TOLERANCE<br>UNLESS OTHERWISE<br>SPECIFIED |       |
|--------------------------------------------|-------|
| .X                                         | ±0.25 |
| .XX                                        | ±0.13 |
| .XXX                                       | ±0.10 |

THIS IS A C.A.D. GENERATED DRAWING  
DO NOT MAKE MANUAL REVISIONS TO MASTER.



| ISSUE NUMBER |   |
|--------------|---|
| ORIGINAL     | ① |



#### NOTES:

#### MATERIAL:

HOUSING: THERMOPLASTIC POLYESTER, UL94V-0

SHELL: STEEL, TIN PLATED

CONTACT: COPPER ALLOY, 30μ GOLD PLATED

OPERATING TEMPERATURE: -55°C to +105°C

CURRENT RATING: 3A PER CONTACT

CONTACT RESISTANCE: 25mΩ MAX.

INSULATOR RESISTANCE: 5000MΩ min.

DIELECTRIC

WITHSTANDING VOLTAGE: 1000V AC rms



THIS SERIES FULLY CONFORMS TO  
THE EUROPEAN UNION DIRECTIVES  
2011/65/EU FOR RoHS COMPLIANCY.



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC  
TORONTO, ONTARIO  
CANADA

THESE DRAWINGS AND SPECIFICATIONS  
ARE THE PROPERTY OF EDAC INC., AND  
SHALL NOT BE REPRODUCED, OR COPIED  
OR USED AS THE BASIS FOR THE  
MANUFACTURE OR SALE OF APPARATUS  
WITHOUT WRITTEN PERMISSION.

|                                                                                                                                                                                           |                                                                                                                                                                                                   |                                 |                    |                |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------|--------------------|----------------|
| 627 SERIES D-SUB CONNECTOR                                                                                                                                                                |                                                                                                                                                                                                   | SW REFERENCE NO.: 627 ASSEMBLY  |                    |                |
|                                                                                                                                                                                           |                                                                                                                                                                                                   | DRAWN: C.B                      | DATE: AUG. 01/2018 |                |
|                                                                                                                                                                                           |                                                                                                                                                                                                   | CHECKED:                        | DATE:              |                |
|  <div>EDAC INC<br/>TORONTO, ONTARIO<br/>CANADA<br/><br/>YOUR CONNECTION TO QUALITY &amp; SERVICE</div> | THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC., AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION. | SCALE: 1:1                      | SHEET 1 OF 1       |                |
|                                                                                                                                                                                           |                                                                                                                                                                                                   | DRAWING NUMBER: 627-009-671-276 |                    | ISSUE<br><br>1 |
|                                                                                                                                                                                           |                                                                                                                                                                                                   | PART NUMBER: 627-009-671-276    |                    |                |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EDAC:

[627-009-671-276](tel:627-009-671-276)