

SECTION ASSEMBLIES AVAILABLE SEPARATE

NO. OF POLES	NO. OF POSITIONS	POLES/ SECTION	INDEX ANGLE	SHORTING PART NUMBERS	NON- SHORTING PART NUMBERS	FIG.
D2D - SERIES DIALYL PHTHALATE INSULATION						
01	02-12	1	30°	D2D-50	D2D-51	DE
02	02-06	2	30°	D2D-52	D2D-53	DL
03	2-05	3	30°	D2D-54	D2D-55	DO
05	2-03	5	30°	D2D-56	D2D-57	DR
D2C - SERIES CERAMIC INSULATION						
01	2-11	1	30°	D2C-20	D2C-21	DB
02	2-05	2	30°	D2C-22	D2C-23	DG
03	2-03	3	30°	D2C-24	D2C-25	DN
04	02	4	30°	D2C-26	D2C-27	DQ
D3C - SERIES CERAMIC INSULATION						
01	2-11	1	30°	D3C-80	D3C-81	DA
02	2-05	2	30°	D3C-82	D3C-83	DH
D4C - SERIES CERAMIC INSULATION						
01	02-12	1	30°	D4C-0	D4C-1	DD
02	02-06	2	30°	D4C-2	D4C-3	DL
03	02-05	3	30°	D4C-4	D4C-5	DO
05	02-03	5	30°	D4C-6	D4C-7	DR
06	02	6	30°	D4C-8	D4C-9	DS
01	02-06	1	60°	D4C-20	D4C-17	DJ
D4G - SERIES GLASS EPOXY INSULATION						
01	2-11	1	30°	D4G-30	D4G-31	DA
02	2-05	2	30°	D4G-32	D4G-33	DG
03	2-03	3	30°	D4G-34	D4G-35	DM
04	2	4	30°	D4G-36	D4G-37	DP
D7C - SERIES CERAMIC INSULATION						
01	2-06	1	30°	D7C-SXD	D7C-XD	DI
01	2-11	1	30°	D7C-SYD	D7C-YD	DB
02	2-05	2	30°	D7C-SRRD	D7C-RRD	DF
01	2-06	1	60°	D7C-SZZD	D7C-ZZD	DK
D7G - SERIES GLASS EPOXY INSULATION						
01	2-11	1	30°	D7G-BD	D7G-JD	DB
02	2-05	2	30°	D7G-SKD	D7G-KD	DH
E4C - SERIES CERAMIC INSULATION						
01	2-17	1	20°	E4C-8	E4C-N8	EA
02	2-08	2	20°	E4C-10	E4C-N10	EB
03	02-05	3	20°	E4C-9	E4C-N9	EC

INDEX ASSEMBLIES AVAILABLE SEPARATE

INDEX ANGLE	NO. OF POSITIONS	NO. OF SECTIONS	PART NUMBERS	PAGE NUMBER
D2 - SERIES				
30°	02-12	1-2	D2-512	20, 21
30°	02-12	3-5	D2-513	20, 21
D3 - SERIES				
30°	02-11	1-4	D3-600	22, 23
D4 - SERIES				
30°	02-12	1-3	D4-300	24, 25
30°	02-12	4-6	D4-301	24, 25
30°	02-12	7-9	D4-302	24, 25
60°	02-06	1-3	D4-304	24, 25
60°	02-06	4-6	D4-305	24, 25
D7 - SERIES				
30°	02-11	1-3	D7-270	30, 31
30°	02-11	4-5	D7-271	30, 31
30°	02-11	6-10	D7-272	30, 31
60°	02-06	1-2	D7-273	30, 31
60°	02-06	3-8	D7-275	30, 31
E4 - SERIES				
20°	02-17	1-6	E4-7	40, 41

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Electroswitch:

[D4G-35](#) [D4G-30](#) [D4G-31](#) [D4G-32](#) [D4G-33](#) [D4C-5](#) [D4C-1](#) [D4C-3](#) [D4C-18](#) [D7G-JD](#) [D2D-55](#) [D4-305](#) [D4C-17](#)
[D4C-2](#) [D4-304](#) [D2D-50](#) [D3C-80](#) [D3C-81](#) [D3C-82](#) [D3C-83](#) [D4C-4](#) [D4C-7](#) [D4C-9](#) [D4G-37](#) [D7C-SXD](#) [D7C-ZZD](#)
[D7G-BD](#) [D7G-KD](#) [E4C-N10](#) [E4C-N8](#) [D2D-54](#) [D2D-56](#) [D2D-57](#) [D4C-0](#) [D4C-20](#) [D4C-6](#) [D4G-34](#) [D4G-36](#) [D7C-](#)
[RRD](#) [D7C-SYD](#) [D7C-SZZD](#) [D7C-XD](#) [D7C-YD](#)