


PVHC4 SERIES ANTI-VANDAL SWITCH


ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS




APPLICATIONS / MARKETS




Audio / Visual



Security Devices



Industrial Controls



Kiosks



Electrical Housewares



Medical Equipment

SPECIFICATIONS

Electrical Rating: 20A, 250VAC
25A, 30VDC
Electrical Life: 50,000 Cycles
Contact Resistance: 100mΩ Max.
Insulation Resistance: 100MΩ @ 500VDC
Dielectric Strength: 1,500VAC
Operating/Storage Temperature: -40°C to 85°C
Travel: 3.50mm
Moisture Protection: IP67
Contact Arrangement: SPST
Actuation Force: 6 N
Panel Thickness: 1-6mm
Mounting Nut Torque: 0.6Nm

FEATURES & BENEFITS

- 19mm diameter panel cutout
- LED option
- Ring or power symbol illumination available
- Multiple function options
- IP67 rated
- SPST

PART NUMBER CONFIGURATOR

Series	Actuator Options	Terminal Options	Function Options	Body Finish Options	Actuator Finish Options	Contact Material Options	Lens Style Options	LED Color Options	Illumination Voltage Options
PVHC4	F - Flat H - High	2 - Solder Lug	3 - 1P Off-On B - 1P Off-(On)	S - Stainless Steel 1 - Black Anodized	S - Stainless Steel 1 - Black Anodized	None - Silver	NONE - Non-Illuminated 3 - Ring Illumination 6 - Ring/Power Symbol Illumination	NONE- Non-Illuminated 0 - White 1 - Red 3 - Green 4 - Blue 5 - Yellow	NONE - Non-Illuminated 3 - 6V 4 - 12V 5 - 24V

NOTES:
() denotes function is momentary

Specifications subject to change without notice 4.17.2024



E-SWITCH®





www.e-switch.com

800.867.2717

1

PVHC4 SERIES ANTI-VANDAL SWITCH

NON-ILLUMINATED BODY DIMENSIONS



E-SWITCH®

www.e-switch.com

800.867.2717

2

ANTI-VANDAL
SWITCHES

DETECTOR
SWITCHES

DIP
SWITCHES

KEYLOCK
SWITCHES

NAVIGATION
SWITCHES

PUSHBUTTON
SWITCHES

ROCKER
SWITCHES

ROTARY
SWITCHES

SLIDE
SWITCHES

SNAP ACTION
SWITCHES




TACTILE
SWITCHES

TOGGLE
SWITCHES

CAP
OPTIONS

PVHC4 SERIES ANTI-VANDAL SWITCH

ILLUMINATED RING BODY DIMENSIONS



E-SWITCH®




www.e-switch.com

800.867.2717

3

PVHC4 SERIES ANTI-VANDAL SWITCH

ILLUMINATED RING/ POWER SYMBOL BODY DIMENSIONS



E-SWITCH®

www.e-switch.com

800.867.2717

4

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[PVHC4F23SS314](#) [PVHC4F2BSS334](#) [PVHC4F23SS](#) [PVHC4F23SS615](#)