



Dimensions



COLOR CODE

1 = Brown (C1)	2 = Slate/Pink	(1)	4 = White	(1)
3 = Blue (C3)	Red/Blue	(2)	Green	(2)
5 = Green/Yellow (Gnd)	White/Green	(3)	Yellow	(3)
	Brown/Green	(4)	Slate	(4)
	White/Yellow	(5)	Pink	(5)
	Yellow/Brown	(6)	Red	(6)
	White/Slate	(7)	Black	(7)
	Slate/Brown	(8)	Violet	(8)



Technical Data

Box Configuration

Ports	8
Channels per Port	2
LED	Yes
Code Type	A
Housing	Orange TPU, flame retardant
Contact	Copper Alloy, Gold Plated
Receptacle Shell	Copper Alloy, Nickel Plated
O-Ring	FKM
Electrical	
Contact Resistance	≤5mΩ
Voltage Rating	10-30V DC
Current Rating	4A per port/12A max. Total
Insulation Resistance	>10 ⁹ Ω
UL File	E485156
Cable Construction	
Conductor Size	3 x 1.0mm ² & 16 x 0.5mm ²
Outer Jacket Material	Zero Halogen PUR
Outer Diameter	.453"
Color	Black

Issue: 1 Issue Date: 9/22/2016 Effective Date: 9/22/2016

Suitable for C-Track	Yes
Environmental	
Degree of Protection	IP 67/ NEMA 6P
Operating Temperature Range	-15C (+5F)/ +80C (+176F)
RoHS	All materials used in the manufacture of this part meet the requirements of European Directive 2011/65/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Exemption used; 6a.
REACH Regulation (EC 1907/2006)	This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item.
Accessories Included	
2 Dust Covers for unused sockets	
10 attachable labels	
Ordering Information	Description Quantity
910-5M NC032	5 Meters Each
910-10M NC032	10 Meters Each
910-CN NC032	Connectorized Each

Although Alpha Wire (“Alpha”) makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Alpha provides the information and specification herein on an “AS IS” basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specification described herein.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha Wire:](#)

[910-CN NC032](#)