

TACT
SWITCHESNAVIGATION
SWITCHESPUSHBUTTON
SWITCHESTOGGLE
SWITCHESROCKER
SWITCHESSLIDE
SWITCHESSNAP-ACTION
SWITCHESDIP
SWITCHESKEYLOCK
SWITCHESROTARY
SWITCHESDETECTOR
SWITCHESCAP
OPTIONS

SERIES EG SWITCHES

SLIDE SWITCHES



SPECIFICATIONS

Contact Resistance:	Less than 20 milliohms
Insulation Resistance:	500VDC – 100 milliohms
Dielectric Strength:	500V AC for 1 minute between any terminal and frame
Operating Temperature:	-20°C to +70°C (-4°F to +158°F)

FEATURES & BENEFITS

- ▶ Variety of package styles & sizes
- ▶ Up to 6 poles
- ▶ Variety of functions
- ▶ Positive detent
- ▶ SMT options

APPLICATIONS/MARKETS

- ▶ Computer servers/peripherals
- ▶ Consumer electronics
- ▶ Instrumentation
- ▶ Test & measurement

MATERIALS

Contact: Silver plated copper alloy

▶ ▶ ▶ Example Ordering Number
EG-1201A



HOW TO ORDER

SERIES
EG


MODEL NO.
□ □ □ □ □

Specifications subject to change without notice.

EG 1201





PANEL MOUNT




SCHEMATIC

Model No.	L
EG1201	4
EG1201A	5.5

EG 1205



PANEL MOUNT



SCHEMATIC






Model No.	L
EG1205	4
EG1205A	5.5








EG 1206







Model No.	L
EG1206	3
EG1206A	6







EG 1213




EG 1218







CAP
OPTIONS


P.C. MOUNTING







SCHEMATIC




P.C. MOUNTING



SCHEMATIC



P.C. MOUNTING






SCHEMATIC

TACT
SWITCHESNAVIGATION
SWITCHESPUSHBUTTON
SWITCHESTOGGLE
SWITCHESROCKER
SWITCHESSLIDE
SWITCHESSNAP-ACTION
SWITCHESDIP
SWITCHESKEYLOCK
SWITCHESROTARY
SWITCHESDETECTOR
SWITCHESCAP
OPTIONS

SERIES EG SWITCHES

SLIDE SWITCHES

EG 1270






P.C. MOUNTING




SCHEMATIC

EG 1271







P.C. MOUNTING




SCHEMATIC

Model No.	L
EG1271	2
EG1271A	4.4

EG 1302







P.C. MOUNTING




SCHEMATIC

Model No.	L
EG1302	6
EG1302A	9

EG 1307







P.C. MOUNTING




SCHEMATIC

EG 1313



P.C. MOUNTING







SCHEMATIC


EG 2201



Model No.	L
EG2201	3
EG2201A	6
EG2201B	9
EG2201C	12
EG2201D	4.5



P.C. MOUNTING



SCHEMATIC

TACT
SWITCHESNAVIGATION
SWITCHESPUSHBUTTON
SWITCHESTOGGLE
SWITCHESROCKER
SWITCHESSLIDE
SWITCHESSNAP-ACTION
SWITCHESDIP
SWITCHESKEYLOCK
SWITCHESROTARY
SWITCHESDETECTOR
SWITCHESCAP
OPTIONS





SERIES EG SWITCHES

SLIDE SWITCHES


EG 2202



Model No.	L
EG2202	5
EG2202A	7.5
EG2202B	9




P.C. MOUNTING







SCHEMATIC


EG 2205



Model No.	L
EG2205	4
EG2205A	2







P.C. MOUNTING




SCHEMATIC

EG 2207



P.C. MOUNTING







SCHEMATIC




EG 2208



Model No.	L
EG2208	4
EG2208A	6




P.C. MOUNTING







SCHEMATIC


EG 2209



Model No.	L
EG2209	2
EG2209A	4




P.C. MOUNTING







SCHEMATIC


EG 2210



Model No.	L
EG2210	6
EG2210A	4
EG2210D	2



P.C. MOUNTING



SCHEMATIC



SERIES EG SWITCHES





SLIDE SWITCHES

TACT
SWITCHESNAVIGATION
SWITCHESPUSHBUTTON
SWITCHESTOGGLE
SWITCHESROCKER
SWITCHESSLIDE
SWITCHESSNAP-ACTION
SWITCHESDIP
SWITCHESKEYLOCK
SWITCHESROTARY
SWITCHESDETECTOR
SWITCHESCAP
OPTIONS


EG 2211



Model No.	L
EG2211	4
EG2211A	2







P.C. MOUNTING




SCHEMATIC

EG 2214







P.C. MOUNTING




SCHEMATIC

EG 2215



P.C. MOUNTING







SCHEMATIC


Model No.	L
EG2215	3.5
EG2215A	6



EG 2219







P.C. MOUNTING




SCHEMATIC

EG 2301







P.C. MOUNTING




SCHEMATIC

EG 2303



P.C. MOUNTING



SCHEMATIC





CAP
OPTIONS



EG 2315




Model No.	L
EG2315	3.5
EG2315A	6







P.C. MOUNTING

SCHEMATIC




EG 2319







P.C. MOUNTING

SCHEMATIC




EG 2322



P.C. MOUNTING

SCHEMATIC






SERIES EG SWITCHES



SLIDE SWITCHES

TACT
SWITCHESNAVIGATION
SWITCHESPUSHBUTTON
SWITCHESTOGGLE
SWITCHESROCKER
SWITCHESSLIDE
SWITCHESSNAP-ACTION
SWITCHESDIP
SWITCHESKEYLOCK
SWITCHESROTARY
SWITCHESDETECTOR
SWITCHESCAP
OPTIONS


EG 2323



Model No.	Mtg. Hole
EG2323	None
EG2323A	M2.6 x P0.45






P.C. MOUNTING




SCHEMATIC

EG 2324



P.C. MOUNTING





SCHEMATIC


EG 2325



Model No.	L
EG2325	2
EG2325A	6






P.C. MOUNTING



SCHEMATIC






EG 2601



P.C. MOUNTING

Model No.	L	"A"
EG2601	9.8	None
EG2601A	9.8	M2.6 x P0.45
EG2601B	6.5	M2.6 x P0.45
EG2601C	6.5	None





SCHEMATIC




EG 4208



Model No.	L
EG4208	4
EG4208A	6





P.C. MOUNTING






SCHEMATIC

EG 4311



P.C. MOUNTING



SCHEMATIC





SERIES EG SWITCHES




SLIDE SWITCHES

TACT
SWITCHESNAVIGATION
SWITCHESPUSHBUTTON
SWITCHESTOGGLE
SWITCHESROCKER
SWITCHESSLIDE
SWITCHESSNAP-ACTION
SWITCHESDIP
SWITCHESKEYLOCK
SWITCHESROTARY
SWITCHESDETECTOR
SWITCHESCAP
OPTIONS


EG 4319



Model No.	L
EG4319	5
EG4319A	6







P.C. MOUNTING




SCHEMATIC

EG 6201



P.C. MOUNTING



SCHEMATIC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[EG2601](#) [EG2601C](#)