



Wire connector TA2.8 1x 250..750kcmil; 2x 250kcmil for 1 cable 250 - 750 kcmil or 2 cables 250 kcmil 3 units accessories for: 3VA53, 3VA63 3VA54 400A, 3VA64 400A

Model	
product brand name	SETRON
accessories	Wire connector
General technical data	
designation / of the terminal	TA2.8
type of electrical connection / with control wire tap	No
Connections according UL	
permissible temperature / of connectable conductor / according to UL 486A-486B	90 °C
stripped length	1.5 in
connectable conductor cross-section	
• for copper cable / stranded / minimum	250 kcmil
• for copper cable / stranded / maximum	750 kcmil
• for copper cable / finely stranded / minimum	250 kcmil
• for copper cable / finely stranded / maximum	750 kcmil
• for aluminum cable / stranded / minimum	250 kcmil
• for aluminum cable / stranded / maximum	750 kcmil
tightening torque / when using copper cables	
• stranded	Cu 410 lb-in/Al 375 lb-in
• finely stranded	Cu 410 lb-in/Al 375 lb-in
Further information	

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9373-0JJ24>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9373-0JJ24>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9373-0JJ24

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

1/13/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3VA93730JJ24](#)