

ASIsafe CD (V3) for AS-i Safety monitor contains configuration software ASIMON V3.05 Suitable for Windows XP, Vista, 7, 8, 8.1 (32/64 bit); 10 Pro, 10 Enterpr. (64 bit); Win Server 2012, 2016 (64 bit).



General technical data		
product designation		ASIsafe CD (V3) for AS-i safety monitor, includes ASIMON configuration software
software version		V 3.05
product description		parameterization, commissioning and diagnostic software for AS-Interface safety monitor
national language of the software		German / English / French / Spanish / Italian / Japanese / Swedish
product license		Single License for 1 installation
software class		B
target system		AS-Interface safety monitor
Features		
product component component library		No
- product function diagnostics function - product function controlled positioning - product function simulation function - product function technological function - product function analysis function - product function movement function - product function data acquisition function - product function commissioning function - product function communication function - product function project planning function - Product function maintenance function - product function evaluation function - product function parameterizing function		Yes No No Yes No No No Yes Yes Yes No No Yes
Requirements		
processor clock frequency minimum	Hz	800
storage capacity		
on hard disk required	Mbyte	32
of the main memory or RAM minimum	Mbyte	32
design of the drive/storage medium required		
CD-ROM		Yes
floppy disk		No
DVD drive		No
Graphics card		
vertical image resolution of the graphics card	pixel	768
horizontal image resolution of the graphics card	pixel	1 024
number of colors of the graphics card		256
Software		

operating system required		Windows 11; Windows 10 Professional 64-bit version 1607; Windows 10 Enterprise 64-bit version 1709; Windows XP, Vista, 7, 8, 8.1 (32/64-bit); Windows Server 2012 R2 SP1 StdE 64-bit; Windows Server 2016 Standard 64-bit
browser software required		no
viewer software required		no

Certificates/ approvals

General Product Approval	EMV	Marine / Shipping
--------------------------	-----	-------------------



[Confirmation](#)



other	Environment
-------	-------------

[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1802-2FB06-0GA1>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK1802-2FB06-0GA1>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK1802-2FB06-0GA1>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK1802-2FB06-0GA1&lang=en

last modified:

9/9/2022

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RK18022FB060GA1](#)