











3-phase busbars Modular spacing 55 mm for 2 switches and accessories Fork shape connections



suitability for use		circuit-breakers 3RV2	
General technical data			
size of the circuit-breaker	S00, S0		
Substance Prohibittance (Date)	07/01/2006		
number of poles for main current circuit	3		
operational current rated value	63 A		
Safety related data			
protection class IP on the front according to IEC 60529	IP20		
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front		
Connections/ Terminals			
type of electrical connection for main current circuit	screw-type terminals		
Approvals Certificates			
General Product Approval		Declaration of Conformity	Test Certificates
<a href="#">Confirmation</a>		   	<a href="#">Special Test Certificate</a>
Test Certificates	Marine / Shipping		other
<a href="#">Type Test Certificates/Test Report</a>	   		<a href="#">Confirmation</a>
other	Environment		
	<a href="#">Environmental Confirmations</a>		

Further information

Siemens has decided to exit the Russian market (see here).  
<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.  
Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV1915-2AB>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV1915-2AB>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RV1915-2AB>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RV1915-2AB&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV1915-2AB&lang=en)



last modified:

2/9/2022 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

3RV19152AB