



Galvanic isolation plate

product brand name	SIRIUS
product category	Galvanic isolation plates
product designation	Galvanic isolation plate
design of the product	For electrical separation of different potentials when devices of different types are installed side by side

General technical data

display version LED	No
product component <ul style="list-style-type: none">semi-conductor output	No
flammability class of enclosure material	UL94 V-0
reference code according to IEC 81346-2	F
Substance Prohibitance (Date)	03/25/2015
product component plug-in socket	No

Connections/ Terminals

product function removable terminal	No
-------------------------------------	----

Installation/ mounting/ dimensions

height	93 mm
width	2 mm
depth	77 mm

Ambient conditions

ambient temperature <ul style="list-style-type: none">during operationduring storageduring transport	<div>-25 ... +60 °C</div> <div>-40 ... +85 °C</div> <div>-40 ... +85 °C</div>
--	---

Certificates/ approvals

General Product Approval	Declaration of Conformity	Marine / Shipping
--------------------------	---------------------------	-------------------



[Confirmation](#)



other

[Confirmation](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RQ3900-0A>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RQ3900-0A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/ww/en/ps/3RQ3900-0A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RQ3900-0A&lang=en

Characteristic: Derating

<https://support.industry.siemens.com/cs/ww/en/ps/3RQ3900-0A/manual>



last modified:

5/6/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

3RQ39000A