



Figure similar

3RV29 infeed system Expansion set for 3 motor starters including expansion plug  
Size S00 and S0 includes 1x 3RV2917-4B 3x 3RV2917-5AA00 3x 3RV2927-5AA00 3x 3RV2927-7AA00

General technical data		
surge voltage resistance rated value		6 kV
thermal current		63 A
Substance Prohibitance (Date)		10/01/2009
operating voltage at AC rated value		500 V
UL/CSA ratings		
operating voltage at AC according to UL rated value		600 V
Ambient conditions		
ambient temperature during operation		-20 ... +60 °C
Safety related data		
protection class IP on the front according to IEC 60529		IP00; IP20 when using finely stranded conductor cross-section 6 mm² and end sleeve (with plastic collar) or conductor cross-section ≥ 10 mm² at the supply terminal
touch protection on the front according to IEC 60529		finger-safe when using finely stranded conductor cross-section 6 mm² and end sleeve (with plastic collar) or conductor cross-section ≥ 10 mm² at the supply terminal
Short-circuit protection		
short-circuit rating		corresponds to the installed circuit breaker or load feeder
Approvals Certificates		
General Product Approval	Marine / Shipping	other

[Confirmation](#)



[Confirmation](#)



### Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2907-4BB00>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2907-4BB00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RV2907-4BB00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RV2907-4BB00&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2907-4BB00&lang=en)

---

last modified:

7/6/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3RV29074BB00](#)