



door-coupling rotary operating mechanism IP64 for circuit breaker size S00...S3, black 330 mm shaft with support !!! product phase-out !!! successor type is 3RV2926-1K drilling pattern changes

product brand name	SIRIUS		
product designation	door-coupling rotary operating mechanism		
design of the product	standard		
suitability for use	Circuit breaker S00, S0, S2, S3		
General technical data			
size of the circuit-breaker	S00, S0, S2, S3		
product feature can be locked into OFF position	Yes		
operating frequency maximum	15 1/h		
certificate of suitability	CE / UL / CSA		
Substance Prohibittance (Date)	07/01/2006		
control version of the switch operating mechanism	long shaft		
Ambient conditions			
ambient temperature			
• during operation	-20 ... +70 °C		
• during storage	-50 ... +80 °C		
Actuator			
product feature interlock	Yes		
color of the actuating element	black		
Installation/ mounting/ dimensions			
mounting position	any		
fastening method	screw fixing		
height	66 mm		
width	66 mm		
depth	50 mm		
length	330 mm		
diameter	22.5 mm		
required spacing			
• for grounded parts			
— forwards	0 mm		
— backwards	0 mm		
— upwards	0 mm		
— at the side	0 mm		
— downwards	0 mm		
Approvals Certificates			
General Product Approval		Declaration of Conformity	Test Certificates

[Confirmation](#)



[Type Test Certificates/Test Report](#)



[Confirmation](#)



Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2926-0K>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2926-0K>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RV2926-0K>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2926-0K&lang=en



last modified:

12/23/2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

3RV29260K