

door-coupling rotary operating mechanism for circuit breaker size S3 handle gray
new design !!! product phase-out !!! successor type is 3RV2946-3B drilling pattern
changes

| | | | |
|---|--|---------------------------|-------------------|
| product brand name | SIRIUS | | |
| product designation | door-coupling rotary operating mechanism for heavy-duty operating conditions | | |
| design of the product | standard | | |
| suitability for use | circuit-breakers S3 | | |
| General technical data | | | |
| size of the circuit-breaker | S3 | | |
| product feature can be locked into OFF position | Yes | | |
| operating frequency maximum | 15 1/h | | |
| certificate of suitability | CE / UL / CSA | | |
| Substance Prohibitance (Date) | 07/01/2006 | | |
| Ambient conditions | | | |
| ambient temperature | | | |
| • during operation | -20 ... +70 °C | | |
| • during storage | -50 ... +80 °C | | |
| Actuator | | | |
| product feature interlock | Yes | | |
| color of the actuating element | gray | | |
| Installation/ mounting/ dimensions | | | |
| mounting position | any | | |
| fastening method | screw fixing | | |
| height | 75 mm | | |
| width | 75 mm | | |
| depth | 78 mm | | |
| length | 300 mm | | |
| diameter | 40 mm | | |
| required spacing | | | |
| • for grounded parts | | | |
| — forwards | 0 mm | | |
| — backwards | 0 mm | | |
| — upwards | 0 mm | | |
| — at the side | 0 mm | | |
| — downwards | 0 mm | | |
| Approvals Certificates | | | |
| General Product Approval | | Declaration of Conformity | Test Certificates |

[Confirmation](#)



[Type Test Certificates/Test Report](#)

[Confirmation](#)**Further information**

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2946-2B>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2946-2B>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RV2946-2B>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2946-2B&lang=en



last modified:

12/23/2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3RV29462B](#)