



door-coupling rotary operating mechanism for circuit breaker size S00/S0 handle gray new design !!! product phase-out !!! successor type is 3RV2926-3B drilling pattern changes

product brand name	SIRIUS
product designation	door-coupling rotary operating mechanism for heavy-duty operating conditions
design of the product	standard
suitability for use	circuit-breakers S0
General technical data	
size of the circuit-breaker	S0
product feature can be locked into OFF position	Yes
operating frequency maximum	15 1/h
certificate of suitability	CE / UL / CSA
Substance Prohibittance (Date)	07/01/2006
Ambient conditions	
ambient temperature	
• during operation	-20 ... +70 °C
• during storage	-50 ... +80 °C
Actuator	
product feature interlock	Yes
color of the actuating element	gray
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw fixing
height	75 mm
width	75 mm
depth	78 mm
length	300 mm
diameter	40 mm
required spacing	
• for grounded parts	
— forwards	0 mm
— backwards	0 mm
— upwards	0 mm
— at the side	0 mm
— downwards	0 mm
Approvals Certificates	
General Product Approval	
Declaration of Con-	
formity	
Test Certificates	
Marine / Shipping	

[Confirmation](#)



[Type Test Certificates/Test Report](#)



[Confirmation](#)**Further information**

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2926-2B>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2926-2B>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RV2926-2B>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2926-2B&lang=en



last modified:

12/23/2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

3RV29262B