



Disconnecter module for circuit breaker Size S00/S0

product brand name	SIRIUS
product designation	disconnecter module
design of the product	visible isolating distance, can be locked in disengaged position
suitability for use	motor circuit breaker

General technical data	
size of the circuit-breaker	S0
certificate of suitability	CE / UL / CSA / CCC
Substance Prohibitance (Date)	10/01/2009

Ambient conditions	
ambient temperature	
• during operation	-20 ... +70 °C
• during storage	-50 ... +80 °C

Installation/ mounting/ dimensions	
height	51 mm
width	45 mm
depth	94 mm

Connections/ Terminals	
connectable conductor cross-section for main contacts	
• solid or stranded	0 ... 0 mm²
• stranded	0 ... 0 mm²
• finely stranded with core end processing	0 ... 0 mm²
• finely stranded without core end processing	0 ... 0 mm²
AWG number as coded connectable conductor cross section for main contacts	0 ... 0

Approvals Certificates		
General Product Approval	Declaration of Conformity	Test Certificates

[Confirmation](#)



[Type Test Certificates/Test Report](#)

Test Certificates	Marine / Shipping
-------------------	-------------------

[Special Test Certificate](#)



Marine / Shipping	other	Railway
-------------------	-------	---------



[Confirmation](#)



[Vibration and Shock](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2928-1A>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2928-1A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RV2928-1A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2928-1A&lang=en



last modified:

12/21/2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

3RV29281A