



Figure similar

communication module PROFINET High-Feature with integrated switch

product brand name	SIRIUS		
product category	Communication modules		
product designation	Communication module		
design of the product	PROFINET High Feature with integrated switch		
manufacturer's article number • of soft starter	3RW55		
General technical data			
reference code according to IEC 81346-2	A		
Substance Prohibittance (Date)	02/11/2019		
Installation/ mounting/ dimensions			
mounting position	any		
fastening method	screw fixing		
height	126 mm		
width	28 mm		
depth	82 mm		
weight without packaging	0.1 kg		
Ambient conditions			
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog		
ambient temperature • during operation • during storage and transport	-25 ... +60 °C; observe derating of basic unit above 40 °C -40 ... +80 °C		
environmental category • during operation according to IEC 60721 • during storage according to IEC 60721 • during transport according to IEC 60721	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6 1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4 2K2, 2C1, 2S1, 2M2 (max. height of fall 0.8 m)		
Safety related data			
protection class IP on the front according to IEC 60529	IP20		
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front		
Certificates/ approvals			
General Product Approval		For use in hazard-ous locations	Declaration of Con-formity



[Confirmation](#)



[Explosion Protection Certificate](#)



Declaration of Conformity	Test Certificates	Marine / Shipping
---------------------------	-------------------	-------------------



[Type Test Certificates/Test Report](#)



other

[Confirmation](#)

[PROFINET-Certification](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5950-0CH00>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5950-0CH00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RW5950-0CH00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW5950-0CH00&lang=en

Characteristic: Tripping characteristics, I²t, Let-through current



<https://support.industry.siemens.com/cs/ww/en/ps/3RW5950-0CH00/char>

Characteristic: Installation altitude


<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5950-0CH00&objecttype=14&gridview=view1>

Simulation Tool for Soft Starters (STS)

<https://support.industry.siemens.com/cs/ww/en/view/101494917>



-A



-X31

-X1:P1

-X1:P2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3RW59500CH00](#)