

Aux switch module rot op mech 2 x leading to "ON" Accessory for: 3VA1
100/160/250



| Model | |
|--|--|
| product brand name | SETRON |
| product designation | Auxiliary switch module, rotary operator |
| design of the product | Accessories for 3VA circuit breakers |
| accessories | Auxiliary switch module |
| General technical data | |
| degree of pollution | 3 |
| overvoltage category | III |
| Voltage | |
| surge voltage resistance | 4 kV |
| operating voltage / at AC / according to CSA and UL | 230 V |
| operating voltage / at DC / according to CSA and UL | 24 V |
| operating voltage / at AC / at 50 Hz / rated value / minimum | 230 V |
| operating voltage / at DC / rated value / minimum | 250 V |
| Current | |
| thermal current | 5 A |
| operational current | |
| • at AC-12 / at 12 V | 5 A |
| • at AC-12 / at 24 V | 5 A |
| • at AC-12 / at 48 V | 5 A |
| • at AC-12 / at 125 V | 5 A |
| • at AC-12 / at 220/240 V | 5 A |
| • at DC-13 / at 12 V | 0.2 A |
| • at DC-13 / at 24 V | 0.2 A |
| • at DC-13 / at 48 V | 0.2 A |
| • at DC-13 / at 110 V | 0.2 A |
| • at DC-13 / at 250 V | 0.2 A |
| • at AC-15 / at 12 V | 2 A |
| • at AC-15 / at 24 V | 2 A |
| • at AC-15 / at 48 V | 2 A |
| • at AC-15 / at 125 V | 2 A |
| • at AC-15 / at 220/240 V | 2 A |
| Mechanical Design | |
| height | 37.35 mm |
| width | 62.3 mm |
| depth | 45 mm |
| ambient temperature / during operation | |
| • minimum | -25 °C |
| • maximum | 70 °C |
| ambient temperature / during storage | |

- minimum
- maximum

-40 °C

80 °C

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9257-0GX10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9257-0GX10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9257-0GX10


CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





last modified:

8/15/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3VA92570GX10](#)