

USB port, 22 mm, plastic with metal front ring, sand gray



|                          |                                            |
|--------------------------|--------------------------------------------|
| product brand name       | SIRIUS ACT                                 |
| product designation      | USB port                                   |
| design of the product    | USB 3.0                                    |
| product type designation | 3SU1                                       |
| product line             | Plastic with metal front ring, matt, 22 mm |

### Actuator

|                                         |          |
|-----------------------------------------|----------|
| outer diameter of the actuating element | 29.45 mm |
|-----------------------------------------|----------|

### General technical data

|                                |            |
|--------------------------------|------------|
| protection class IP            | IP65       |
| Substance Prohibitation (Date) | 10/01/2014 |

### Ambient conditions

|                                |                |
|--------------------------------|----------------|
| ambient temperature            |                |
| • during operation             | 70 ... -25 °C  |
| • during storage and transport | -40 ... +80 °C |

### Installation/ mounting/ dimensions

|                                   |          |
|-----------------------------------|----------|
| shape of the installation opening | round    |
| mounting diameter                 | 22.3 mm  |
| mounting height                   | 11.7 mm  |
| installation width                | 29.45 mm |
| installation depth                | 28.35 mm |

### Accessories

|                       |           |
|-----------------------|-----------|
| material of accessory | Metal     |
| color of accessory    | sand gray |

### Certificates/ approvals

|                          |                           |                   |
|--------------------------|---------------------------|-------------------|
| General Product Approval | Declaration of Conformity | Test Certificates |
|--------------------------|---------------------------|-------------------|

[Confirmation](#)



[Type Test Certificates/Test Report](#)

|                   |       |
|-------------------|-------|
| Marine / Shipping | other |
|-------------------|-------|



[Confirmation](#)

### Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

**Siemens is working on the renewal of the current EAC certificates.**

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

**Information on the packaging**

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<https://www.siemens.com/ic10>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1930-0GA80-0AA0>

**Cax online generator**


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1930-0GA80-0AA0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1930-0GA80-0AA0>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1930-0GA80-0AA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1930-0GA80-0AA0&lang=en)



last modified:

4/4/2022 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3SU19300GA800AA0](#)