



SIRIUS Motor Starter ES 2007 Basic Floating License for one user
Engineering software Software on CD License key on USB stick
Class A 3 languages (de, en, fr) Executable in: Win 7 SP1 / Win 10
- 64 Bit Prof./Ultimate/Enterprise Win Server 2008 R2 Std. SP1 /
2012 R2 / 2016 - 64 bit Communications via system interface
Content: Set (1xDVD + 1x USB)

General technical data		
product designation		Motor Starter ES 2007 BASIC Floating License
software version		2007
product description		motor starter parameterization, commissioning and diagnostic software for High Feature starters of the ECOFAST, ET 200S, ET 200pro and M200D families
national language of the software		german / english / french
product variations		Basic
product license		floating license for 1 user
software class		A
target system		ECOFAST, SIMATIC ET 200S, ET 200pro, M200D
Features		
product component component library		No
- product function diagnostics function - product function controlled positioning - product function simulation function - product function technological function - product function analysis function - product function movement function - product function data acquisition function - product function commissioning function - product function communication function - product function project planning function - Product function maintenance function - product function evaluation function - product function parameterizing function		No No No No No No Yes Yes Yes No Yes Yes Yes
Requirements		
processor clock frequency		
minimum	MHz	1 000
storage capacity		
- on hard disk required - of the main memory or RAM minimum	Mbyte Mbyte	280 2 000
design of the drive/storage medium required		
- CD-ROM - floppy disk - DVD drive		Yes No No
Graphics card		
vertical image resolution of the graphics card	pixel	768
horizontal image resolution of the graphics card	pixel	1 024
number of colors of the graphics card		256

Software		
operating system required		Windows 7 SP1 64-bit Ultimate, Professional and Enterprise (standard installation), Windows 10 64-bit Pro and Enterprise, Windows 2008 Server R2 StdE SP1 64-bit Standard, Windows 2012 Server R2 StdE SP1 64-bit Standard, Windows 2016 64-bit Server Essentials, Standard, Datacenter
browser software required		no
viewer software required		no
Certificates/ approvals		
other		

[Confirmation](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3ZS1310-4CC10-0YA5>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3ZS1310-4CC10-0YA5>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3ZS1310-4CC10-0YA5>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3ZS1310-4CC10-0YA5&lang=en

last modified:

1/18/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3ZS13104CC100YA5](#)