

Wire connector TC1.1 14 AWG...2/0 Cu 4 units accessories for: 3VA5 125



| Model | |
|--|--|
| product brand name | SETRON |
| product designation | accessories |
| design of the product | circular conductor terminal |
| accessories | Wire connector |
| General technical data | |
| designation / of the terminal | TC1.1 |
| type of electrical connection / with control wire tap | No |
| Connections according IEC | |
| stripped length | 12,2 mm |
| Connections according UL | |
| permissible temperature / of connectable conductor / according to UL 486A-486B | 90 °C |
| stripped length | 0.48 in |
| connectable conductor cross-section | |
| • for copper cable / solid / minimum | 14 AWG |
| • for copper cable / solid / maximum | 10 AWG |
| • for copper cable / stranded / minimum | 14 AWG |
| • for copper cable / stranded / maximum | 2/0 AWG |
| • for copper cable / finely stranded / minimum | 14 AWG |
| • for copper cable / finely stranded / maximum | 2/0 AWG |
| tightening torque / when using copper cables | |
| • solid | 14 AWG: 25 lb-in 12 AWG: 35 lb-in 10 AWG: 55 lb-in |
| • stranded | 14 AWG: 25 lb-in 12 AWG: 35 lb-in 10 AWG - 2/0: 55 lb-in |
| • finely stranded | 14 AWG: 25 lb-in 12 AWG: 35 lb-in 10 AWG - 2/0: 55 lb-in |
| Further information | |

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9134-0JD11>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9134-0JD11>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9134-0JD11

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

8/15/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3VA91340JD11](#)