

LED, Base BA 15d, blue, 24 V AC/DC, accessory for signaling columns, with diameters 50 mm and 70 mm



|                                                      |  |                |                           |
|------------------------------------------------------|--|----------------|---------------------------|
| product brand name                                   |  | SIRIUS         |                           |
| product designation                                  |  | LED            |                           |
| General technical data                               |  |                |                           |
| type of voltage of the operating voltage             |  | AC/DC          |                           |
| operating voltage                                    |  |                |                           |
| • 1 at DC rated value                                |  | 24 V           |                           |
| • 1 at AC at 50 Hz rated value                       |  | 24 V           |                           |
| • 1 at AC at 60 Hz rated value                       |  | 24 V           |                           |
| relative positive tolerance of the operating voltage |  | 10 %           |                           |
| relative negative tolerance of the operating voltage |  | -15 %          |                           |
| consumed current maximum                             |  | 15 mA          |                           |
| reference code according to EN 61346-2               |  | P              |                           |
| Lamp                                                 |  |                |                           |
| type of light source                                 |  | LED            |                           |
| light intensity                                      |  | 0.21 cd        |                           |
| socket design                                        |  | BA 15d         |                           |
| Enclosure                                            |  |                |                           |
| height                                               |  | 45 mm          |                           |
| width                                                |  | 20 mm          |                           |
| outer diameter of the signal column element          |  | 70 mm          |                           |
| color                                                |  | blue           |                           |
| Ambient conditions                                   |  |                |                           |
| ambient temperature during operation                 |  | -20 ... +60 °C |                           |
| Certificates/ approvals                              |  |                |                           |
| General Product Approval                             |  | EMC            | Declaration of Conformity |
|                                                      |  |                | other                     |

[Confirmation](#)



[Confirmation](#)

### Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD4428-6XF>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD4428-6XF>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WD4428-6XF>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=8WD4428-6XF&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD4428-6XF&lang=en)

-P



last modified:

1/18/2021 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

8WD44286XF