



Figure similar

OUTPUT CHOKE; PHASES:3; UN1(V):400; ITHMAX 1(A) / F1(HZ):13,5 /50; F TAKT(KHZ):7; I LN (A):12,2; LN(MH):1,7; UK(%):3,13; TA/ISOKL:40 /B; IP00; TYPE OF TERMINALS:SCREW CONNECTION; EN 61558-2-20 >UL/CSA-RECOGNIZED< >CHOKE<

General technical data		
product designation		output reactor
product brand name		SIDAC
phase number		3
type of voltage		AC
operating voltage rated value		
• maximum	V	400
operating frequency rated value		
• minimum	Hz	0
• maximum	Hz	50
•		
— operational current at AC rated value	A	12.2
— current at AC maximum	A	13.5
inductivity rated value	H	0.0017
power loss [W] of the coil	W	26.9
power loss [W] of the iron core	W	14
clock frequency		
• rated value	Hz	7 000
Mechanical data		
type of electrical connection for main current circuit		screw-type terminals
width	m	0.17
height	m	0.15
depth	m	0.12
Ambient conditions		
thermal class according to IEC 60085		B
ambient temperature rated value	°C	40
protection class IP		IP00
Certificates/ approvals		
General Product Approval	Declaration of Conformity	other



[Confirmation](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4EP3883-2DS00>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EP3883-2DS00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4EP3883-2DS00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4EP3883-2DS00&lang=en

last modified:

2/11/2021 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[4EP38832DS00](#)