



Integrated signal lamp, single flash light, w. built-in electronic flash, clear, 115 V AC, Diameter 70 mm

General technical data			
product designation		Flashlight element	
consumed current maximum		22 mA	
type of voltage of the operating voltage		AC	
operating voltage			
• 1 at AC at 50 Hz rated value		115 V	
• 1 at AC at 60 Hz rated value		115 V	
relative positive tolerance of the operating voltage		10 %	
relative negative tolerance of the operating voltage		-10 %	
reference code according to IEC 81346-2		P	
fastening method		Bayonet / flush mounting	
material		PC; PC/ABS; PA	
color		clear	
Mechanical data			
product component light source		Yes	
type of electrical connection		screw-type terminals	
outer diameter of the signal column element		75 mm	
Lamp			
design of the optical signal		flash light	
type of light source		Xenon gas discharge lamp	
light intensity		36 793 cd	
flash frequency		1 Hz	
number of flashes of light element		4 000 000	
Ambient conditions			
ambient temperature during operation		-20 ... +50 °C	
protection class IP		IP65	
depth		31 mm	
height		66 mm	
width		75 mm	
Certificates/ approvals			
General Product Approval		EMC	Declaration of Conformity

[Confirmation](#)



other

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8WD5340-0CE>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=8WD5340-0CE>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8WD5340-0CE>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=8WD5340-0CE&lang=en





last modified:

12/23/2020 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

8WD53400CE