

Metal, selector switch Spring return from left Short lever Position, C Cam 3 position  
Operator only white insert Non-Illuminated UL file E22655 in Vol. 6 (7) Sec. 13 (2)



design of the product	Actuator round
<b>Enclosure</b>	
number of command points	1
delivery state as a kit	No
<b>Actuator</b>	
design of the actuating element	selector switch
material of the actuating element	plastic
type of unlocking device	rotate-to-unlatch mechanism
number of switching positions	3
<b>Front ring</b>	
product component front ring	Yes
design of the front ring	standard
material of the front ring	metal
color of the front ring	chrome
<b>Holder</b>	
material of the holder	Metal
<b>General technical data</b>	
product component	
• light source	No
degree of pollution	1
protection class IP	IP66
operating frequency maximum	600 1/h
<b>Ambient conditions</b>	
ambient temperature	
• during operation	-35 ... +70 °C
• during storage	-40 ... +85 °C
<b>Installation/ mounting/ dimensions</b>	
shape of the installation opening	round
<b>Certificates/ approvals</b>	
<b>Further information</b>	

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52SA2CBB>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=US2:52SA2CBB>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/US2:52SA2CBB>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=US2:52SA2CBB&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:52SA2CBB&lang=en)

---

last modified:

5/31/2021 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

52SA2CBB