

30mm Command/52, Chrome Finish Heavy Duty, Watertight/Oiltight Metal Operator, Round Non-Illuminated Keyed Selector Switch 3 Position, C-CAM Maintained Lock type 506CH with 2 Keys Key Removal - Center Position UL Listed, CSA Certified UL File E22655 in Vol. 6 (7) Sec. 13 (2) NEMA 1, 3, 3R, 4, 4X, 12, 13 & Automotive Standards

| | |
|---|---------------------|
| design of the product | Actuator round |
| Enclosure | |
| number of command points | 1 |
| delivery state as a kit | No |
| Actuator | |
| design of the actuating element | Key-operated switch |
| material of the actuating element | metal |
| type of unlocking device | key unlatching |
| number of switching positions | 3 |
| switch position for key distraction | center |
| lock make | ILLINOIS |
| key number | 506CH |
| Front ring | |
| product component front ring | Yes |
| design of the front ring | standard |
| material of the front ring | metal |
| color of the front ring | chrome |
| Holder | |
| material of the holder | Metal |
| General technical data | |
| product component | |
| • light source | No |
| degree of pollution | 1 |
| protection class IP | IP66 |
| operating frequency maximum | 600 1/h |
| Ambient conditions | |
| ambient temperature | |
| • during operation | -35 ... +70 °C |
| • during storage | -40 ... +85 °C |
| Installation/ mounting/ dimensions | |
| shape of the installation opening | round |
| Certificates/ approvals | |
| Further information | |

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52SC6CHX302>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=US2:52SC6CHX302>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/US2:52SC6CHX302>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:52SC6CHX302&lang=en

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

52SC6CHX302