



AUDIO
TECHNOLOGIES®

XLR CHASSIS CONNECTORS

4 PIN B SERIES - HORIZONTAL PCB MOUNT

Locking horizontal PCB mount 4 pin chassis connector with plastic body and metal faceplate perfect for use in DC power, aviation, communications, and other AV applications.

Other Available Mounting Option: Horizontal PCB Mount



IO-XLR4-M-BH

IO-XLR4-F-BH

SPECIFICATIONS

PRODUCT

Gender: **Male (IO-XLR4-M-BH)**

Female (IO-XLR4-F-BH)

Contacts: **4**

ELECTRICAL

Capacitance Between Contacts: **< 2.5 pF**

Capacitance Between Contact and Ground: **< 3 pF**

Contact Resistance: **< 6 mΩ**

Insulation Resistance: **≥ 5000 MΩ**

Dielectric Strength: **1500V @ 60s**

Current Rating: **4.5A / 50V AC**

Grounding: **Separate ground terminal. Grounds to shell of mating connector and panel**

ENVIRONMENTAL

UL Flammability Rating: **UL94 V-0**

Standard Compliance: **IEC 61076-2-103**

Temperature Range: **-40°C ~ +70° C (-40°F ~ +158°F)**

MECHANICAL

Lifetime: **> 1000 Mating Cycles**

Wiring: **Horizontal PCB Mount**

Locking Device: **Latch Lock**

Mounting Direction: **Rear**

Solderability: **Complies with IEC 60068-2-20**

MATERIAL

Contacts: **Gold Plated Brass**

Ground Terminal: **Nickel Plated Brass**

Shell: **Polyamide**

Shell Finish: **Black**

Push Button: **Nickel Plated Brass**

Latch: **Nickel Plated Carbon Steel**


Faceplate: **Nickel Plated Zinc Alloy**

Product specifications may change without prior notification

Io Audio Technologies® is a registered trademark of Knight Electronics, Inc.
10557 Metric Dr. Dallas, TX 75243 | 214-340-0265 | 800-323-2439 | Fax: 214-340-5870 |
www.ioaudiotكنولوجies.com



Panel Cutout



FEATURES & APPLICATIONS

B Series XLR chassis connectors offer the most cost-effective solution for design-in applications where the termination method is to a printed circuit board. The small footprint makes this our XLR receptacle with the highest packing density available. These connectors feature a compact, all plastic housing with a nickel plated faceplate. Precision machined, one piece, gold plated contacts are standard to help prolong the useful life of the connectors. They also come with a separate nickel plated ground pin that grounds the connector to the panel. The compact form factor of these connectors makes them perfect for situations where space saving is a priority or space for a connector is limited.

Available in 3, 4, or 5 pin, Male or Female variations with options for vertical or horizontal PCB mounting.

PART NUMBER BREAKDOWN:

IO-XLR4-M-BH

Series Identifier

IO-XLR4-M-BH

Number of Pins

IO-XLR4-M-BH

Gender

IO-XLR4-M-BH

Series Identifier

IO-XLR4-M-BH

H = Horizontal PCB Mount

V = Vertical PCB Mount

STANDARDS & CLASSIFICATIONS



Product specifications may change without prior notification

Io Audio Technologies® is a registered trademark of Knight Electronics, Inc.
10557 Metric Dr. Dallas, TX 75243 | 214-340-0265 | 800-323-2439 | Fax: 214-340-5870 |
www.ioaudiotكنولوجies.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Io Audio:](#)

[IO-XLR4-F-BH](#) [IO-XLR4-M-BH](#)