


For Tap Thru and Blind Tap information see chart

| Tapped Thru up to and including these lengths |                                |                 | Longer Lengths |
|-----------------------------------------------|--------------------------------|-----------------|----------------|
| Thread                                        | Aluminum, Brass, Steel & Nylon | Stainless Steel | Tap Each End   |
| 0-80                                          | .375                           | .250            | .187           |
| 2-56                                          | .750                           | .625            | .187           |
| 4-40                                          | 1.00                           | .750            | .250           |
| 6-32                                          | 1.00                           | 1.00            | .375           |
| 8-32                                          | 1.00                           | 1.00            | .437           |
| 10-32                                         | 1.125                          | 1.00            | .500           |
| 12-24                                         | 1.125                          | 1.00            | .500           |
| 25-20                                         | 1.250                          | 1.250           | .625           |

All base materials are RoHS compliant

|                                                                                                                                                                                                                                 |                                                                                                                                                                                                |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Drawing not to scale                                                                                                                                                                                                            | Title: Hex Female Standoff                                                                                                                                                                     |
| Break all sharp edges on outside diameters                                                                                                                                                                                      | Part Number: FC2303-2520-SS                                                                                                                                                                    |
| All base materials are RoHS compliant                                                                                                                                                                                           | Material: Stainless Steel                                                                                                                                                                      |
| Tolerances<br>(Unless Specified)<br><u>Decimal</u> .XXX ± .005<br>.XX ± .010<br><br><u>Fraction</u> ± .005<br><br><u>Angle</u> ± 3°<br><br><u>Millimeters</u> ± .13<br><br><u>Nylon</u> ± .010<br><br><u>Metric Nylon</u> ± .25 | Finish: Plain                                                                                                                                                                                  |
|                                                                                                                                                                                                                                 | <br><br>1235 Tradeport Drive, Orlando, FL 32824<br>Tel: 407-226-2112 Fax: 407-226-3370<br>www.Fascomp.com |
|                                                                                                                                                                                                                                 |                                                                                                                                                                                                |
|                                                                                                                                                                                                                                 |                                                                                                                                                                                                |
|                                                                                                                                                                                                                                 |                                                                                                                                                                                                |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fascomp:](#)

[FC2303-2520-SS](#)