


Captive Screw Type 1 10-32 Thread



Create a part number:

Length	Material	Finish
FCXXXX	XX	XX
_____ - _____ - _____		

Captive Screws - 10-32 Thread

FCXXXX	Length (L)	H.D. +.015 / -.000	S.L. +.010 / -.010	D. +.010 / -.000
FC0161	5/8	7/16	1/4	1/16
FC0162	11/16	7/16	5/16	1/16
FC0163	3/4	7/16	3/8	1/16
FC0164	13/16	7/16	7/16	1/16
FC0165	7/8	7/16	1/2	1/16
FC0166	15/16	7/16	9/16	1/16
FC0167	1	7/16	5/8	1/16
FC0168	1-1/16	7/16	11/16	1/16
FC0169	1-1/8	7/16	3/4	1/16
FC0170	1-3/16	7/16	13/16	1/16
FC0171	1-1/4	7/16	7/8	1/16
FC0172	1-5/16	7/16	15/16	1/16
FC0173	1-3/8	7/16	1	1/16
FC0174	1-7/16	7/16	1-1/16	1/16
FC0175	1-1/2	7/16	1-1/8	1/16
FC0176	1-9/16	7/16	1-3/16	1/16
FC0177	1-5/8	7/16	1-1/4	1/16
FC0178	1-11/16	7/16	1-5/16	1/16
FC0179	1-3/4	7/16	1-3/8	1/16
FC0180	1-13/16	7/16	1-7/16	1/16
FC0181	1-7/8	7/16	1-1/2	1/16
FC0182	1-15/16	7/16	1-9/16	1/16
FC0183	2	7/16	1-5/8	1/16

Material

Material Code (XX)
B Brass
S Steel
SS Stainless Steel

Compatible Finish (XX)

B, S, SS	0 - Plain
B, S	5 - Nickel Plate (QQ-N-290)
B, S	12 - Zinc Clear (ASTM-B-633)
B, S	16 - Electro Tin (MIL-T-10727 TYPE 1)
SS	20 - Passivation (MIL-F-14072D)
B, S, SS	26 - Black Oxide
B, S	28 - Zinc Yellow (ASTM-B-633)

Tolerances Unless otherwise Specified
 .xxx +/- .005
 .xx +/- .010
 Angular +/- 1 Degree
 Linear +/- .005
Break all sharp edges

Source Control Drawing:
 To be produced by
 Fascomp Electronic Hardware



This document is the property of Fascomp Inc. and shall not be reproduced, distributed, or used as a basis for manufacturing without written permission from Fascomp Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fascomp:

[FC0161-SS](#) [FC0163-SS](#) [FC0165-SS](#) [FC0167-SS](#) [FC0169-SS](#) [FC0171-SS](#) [FC0173-SS](#) [FC0175-SS](#) [FC0179-SS](#)
[FC0183-SS](#)