


Hex Thumb Nut



Create a part number:

Length	Material	Finish
FCXXXX	XX	XX
_____ - _____ - _____		

Length Table

FCXXXX	Thread	A +.020 -.020	B +.015 -.015	C Ref	D +.010 -.010	E +.031 -.031
FC7219	2-56	1/4	1/8	1/4	1/8	3/16
FC7220	4-40	5/16	1/8	1/4	1/8	1/4
FC7221	6-32	3/8	1/8	9/32	5/32	11/32
FC7222	8-32	7/16	1/8	9/32	5/32	3/8
FC7223	10-24	1/2	5/32	11/32	3/16	13/32
FC7224	10-32	1/2	5/32	11/32	3/16	13/32
FC7225	1/4-20	9/16	5/32	3/8	7/32	15/32
FC7226	5/16-18	5/8	3/16	13/32	7/32	17/32
FC7227	3/8-16	3/4	7/32	15/32	1/4	5/8

Material

Material Code (XX)
A Aluminum
B Brass
S Steel
SS Stainless Steel

Compatible Finish (XX)

Compatible Finish (XX)
A, B, S, SS 0 - Plain
B, S 5 - Nickel Plate (QQ-N-290)
A 6 - Iridite #14 Gold (MIL-C-5541E)
A 7 - Iridite Clear (MIL-C-5541E)
A 9 - Alodine 1200
B, S 12 - Zinc Clear (ASTM-B-633)
B, S 16 - Electro Tin (MIL-T-10727 TYPE 1)
SS 20 - Passivation (MIL-F-14072D)
A 22 - Clear Anodize (MIL-A-8625-TYPE2) (Sulphuric) Hot Water Seal (Clear)
A 24 - Black Anodize (MIL-A-8625)
B, S, SS 26 - Black Oxide
B, S 28 - Zinc Yellow (ASTM-B-633)

Tolerances
Unless otherwise Specified
 .xxx +/- .005
 .xx +/- .010
 Angular +/- 1 Degree
 Linear +/- .005
Break all sharp edges

This document is the property of Fascomp Inc. and shall not be reproduced, distributed, or used as a basis for manufacturing without written permission from Fascomp Inc.



Source Control Drawing:
 To be produced by
 Fascomp Electronic Hardware

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Fascomp:

[FC7219-A](#) [FC7220-A](#) [FC7221-A](#) [FC7222-A](#) [FC7226-A](#) [FC7226-SS](#) [FC7223-A](#) [FC7223-SS](#) [FC7224-A](#) [FC7224-SS](#) [FC7225-A](#) [FC7225-SS](#) [FC7227-A](#) [FC7227-SS](#) [FC7219-SS](#) [FC7220-SS](#) [FC7221-SS](#) [FC7222-SS](#)